





LOC AI	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-10-007169	01APR2010	MKD	RRP
			C 1	ECR-12-002845	12APR2012	MKD	RRP
			C 2	ECR-13-010494	08 JUL 2013	MKD	RRP

Bemerkungen
NOTES

- | | |
|---|---|
| 1 | Massgebend ist der deutsche Text
ONLY THE GERMAN-LANGUAGE VERSION SHALL BE BINDING |
|  | Lage des Kontaktpunktes auf der Leiterplatte: Abweichung ± 0.4
POSITION OF CONTACT POINT ON BOARD: DEVIATION ± 0.4 |
|  | Kontaktierung zur Drahtmitte um 0.7mm versetzt
CONTACTING 0.7mm DISPLACED TO WIRE CENTRELINE |
|  | Kontaktkammer-Nr.
CONTACT CAVITY # |
|  | Firmenlogo und Leergehäuse-Nr.
ARTWORK LOGO AND HOUSING # (NON LOADED) |
|  | Vierkantloch 2x2 mm wahlweise Rastloch $\varnothing 2.5$ mm
SQUARE HOLE 2x2 mm OPTIONAL LOCKING HOLE $\varnothing 2.5$ mm |
|  | Ausführung nach DIN 60249-2-4
BOARD DESIGN ACCORDING TO DIN 60249-2-4 |
| 8 | Crimp Kontakt-Nr.
Material: CuSn4 926770-1; 926917-1
CRIMP CONTACT #
MATERIAL: CuSn4 |
|  | MATERIAL ACCORDING TO IEC-60335-1 (INCLUDING GWT 750 °C NO FLAME) |

1703129-5	MT-EDGE HOUSING	NATURE
1703129-1	MT-EDGE HOUSING	NATURE
PART-NO.:	DESCRIPTION	COLOUR

Schematische Darstellung des
MT-Edge Gehäuses mit
geschlossenem Deckel
SCHEMATIC DESCRIPTION OF
MT-EDGE HOUSING WITH
CLOSED LID



2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27SEP2004 MAHNKE, B.		TE Connectivity	
DIMENSIONS: mm		CHK 20DEC2004 STREDAK, F.		 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 20DEC2004 BLICHER, M.			
		PRODUCT SPEC 108-18003			
0 PLC ± 1 PLC ±0.2mm 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±°		APPLICATION SPEC 114-18002			
MATERIAL PA6.6 / UL94V-2		WEIGHT 3.920 g			
FINISH		SIZE A2		CAGE CODE	DRAWING NO C-1703129
CUSTOMER DRAWING		RESTRICTED TO		-	
SCALE 5:1		SHEET 1 of 1		REV 2	