


ELECTRICAL SPECIFICATION

PARAMETER	SYMBOL	CONDITIONS	VALUE	UNIT
Nominal Frequency	f_o	$V_{CC} \pm 5\%$	26.000	MHz
Supply voltage, nom.	V_{CC}	$V_{CC} \pm 5\%$	1.8	VDC
Supply current, max	I_s	$V_{CC} \pm 5\%$	2.0	mA
Operating temperature	T_a		-30 ~ +85	°C
Storage temperature	$T(stg)$	Absolute max	-40 ~ +85	°C
Frequency Stability				
vs. Temperature, Max	$\Delta f/f_o(T_a)$	Reference to +25°C ± 2°C (-30 TO 85°C)	±0.5	ppm
vs. Supply Voltage	$\Delta f/f_v$	$V_{CC} \pm 5\%$	±0.2	ppm
vs. Load	$\Delta f/f_L$	Load ±10%	±0.2	ppm
vs. Aging Max	$\Delta f/f_o(year)$	Per Year at +25°C ± 2°C	±1.0	ppm
Initial Frequency Calibration, Max	f_c	Measured at 25°C, Reference to f_o	±2.0	ppm
Output Level, Clipped Sine Wave	-	10K Ohms // 10 pF ±10%	0.8	V _{P-P}
Voltage Control Range	V_c	$V_c = 0.3V_{dc}$ to 1.5Vdc	±5 to ±12	ppm
Start up time, Max	t_s	$V_{OUT} \geq 90\% V_{P-P}$	3.0	ms
Phase noise @ freq. offset, typical.	$E(\Delta f)$	$\Delta f = 1$ KHz	-130	dBc/Hz

MECHANICAL SPECIFICATION



OUTLINE TOLERANCE


IF NOT SPECIFIED:
±0.015" / 0.4mm

PIN FUNCTIONS:

- [1] Vcontrol
- [2] GND
- [3] OUTPUT *
- [4] VCC

* Add a 1000 pF DC-cut capacitor to the output pad of the TCXO.

REFLOW PROFILE



Reflow profile		
Temperature Min Preheat	T _{SMIN}	150°C
Temperature Max Preheat	T _{SMAX}	200°C
Time (T _{SMIN} to T _{SMAX})	t _s	60-180 sec.
Temperature	T _L	217°C
Peak Temperature	T _P	260°C
Ramp-up rate	R _{UP}	3°C/sec max.
Ramp-down rate	R _{DOWN}	6°C/sec max.
Time within 5°C of Peak Temperature	t _p	10 sec.
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.
Time	t _L	60-150 sec.

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
REACH-SVHC	COMPLIANT
RoHS2	6/6 LEAD FREE
TERMINATION FINISH	Au



MARKING

Rx26.0

•A3yw

x – Internal Production ID code

y – Year code

w – Week code

YEAR CODE	
Year	Code
2011	1
2012	2
2013	3
2014	4
2015	5
2016	6
2017	7
2018	8
2019	9

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	a	19	s	37	K
2	b	20	t	38	L
3	c	21	u	39	M
4	d	22	v	40	N
5	e	23	w	41	O
6	f	24	x	42	P
7	g	25	y	43	Q
8	h	26	z	44	R
9	i	27	A	45	S
10	j	28	B	46	T
11	k	29	C	47	U
12	l	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	X
15	o	33	G	51	Y
16	p	34	H	52	Z
17	q	35	I		
18	r	36	J		

APPROVALS

RALTRON	
Created by, date:	KJackson, 6-23-14
Eng. approval, date:	KJackson, 6-23-14
Revision:	A

Raltron Electronics/RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort to ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not assume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.