





	1	2	3	4	5	6	7	
A	④ <u>USB2.0 COMPLIANT</u>							A
B	    NOTES: 1.Material: 1.1 Housing: PBT+30%GF UL94V-0, Color Black 1.2 Shell: SPCC 1.3 Contact :Brass 2. FINISH: 2.1 Contact Area: Selective 15u"Au Solder Area: Tin Plated Under: Ni Plated 3.MECHANICAL: 3.1 Mating Force:3.57kgf Max. 3.2 Unmating Force:1.02kgf Min 3.3 Durability:1500 cycles Min 4.ELECTRICAL: 4.1 Current Rating:1.5A 4.2 Dielectric Strength:500V AC FOR 1 MINUTE 4.3 Contact Resistance:30mΩ Max 4.4 Insulation Resistance:1000 MΩ Min ⑤ 4.5 Voltage Rating: 30VAC ② 5.Operating temperature: -55°C TO +85°C ⑤ 6.Soldering temperature: 235°C, 5 Sec max 7.PACKIING: Tray							B
C								C
D								D
E								E
F								F
G	<div> <div>Scale</div> <div>Free</div> <div>⑤ Update</div> <div>14.11.2019</div> <div>Carson</div> <div></div> <div>Date</div> <div>Name</div> <div>Customer-No.</div> </div> <div> <div>TOLERANCE</div> <div>④ Update</div> <div>24.07.2019</div> <div>Xavier</div> <div>Drawn</div> <div>07.06.2013</div> <div>Winnie</div> <div></div> </div> <div> <div>.X ±0.30</div> <div>③ Change the Pin number</div> <div>03.04.2014</div> <div>Winnie</div> <div>Approved</div> <div>14.11.2019</div> <div>Carson</div> <div>ASSMANN WSW-No.</div> </div> <div> <div>.XX ±0.20</div> <div>② Add the soldering temperature</div> <div>27.12.2013</div> <div>Winnie</div> <div></div> <div></div> <div></div> <div>① AU-Y1008</div> </div> <div> <div>.XXX ±0.10</div> <div>① Update the P/N</div> <div>10.12.2013</div> <div>Winnie</div> <div data-cs="2" data-kind="parent" data-rs="3">  </div> <div></div> <div></div> <div>Drawing-No.</div> </div> <div> <div>DIM TOL</div> <div>① Drawn</div> <div>07.06.2013</div> <div>Winnie</div> <div>ASS 5781 CO</div> <div>rev05</div> </div> <div> <div>X.° ±5°</div> <div>Id.</div> <div>Modification</div> <div>Date</div> <div>Name</div> <div>Replace</div> <div>SHEET</div> </div> <div> <div>Angle TOL</div> <div></div> <div></div> <div></div> <div></div> <div></div> <div></div> </div> <div> <div>UNIT mm</div> <div></div> <div></div> <div></div> <div></div> <div></div> <div></div> </div>							G
H								H
	1	2	3	4	5	6	7	

RoHS compliant