

SENSITRON SEMICONDUCTOR

SS6102A/US thru SS6137A/US

TECHNICAL DATA DATA SHEET 5073, REV. -

Transient Voltage Suppressor Diode, 500W

- Hermetic, non-cavity glass package
- Metallurgically bonded
- Operating and Storage Temperature: -55°C to +175°C


SERIES TYPE	MIN BREAKDOWN VOLTAGE $V_{(BR)}$ @ $I_{(BR)}$		WORKING PEAK REVERSE VOLTAGE VRWM	MAXIMUM REVERSE CURRENT I_{R1}	MAX. CLAMP. VOLTAGE VC @ I_P tp = 1ms	MAX. PEAK PULSE CURRENT I_P	MAX. TEMP. COEFFICIENT $V_{(BR)}$
500W	Vdc	mA dc	Vdc	μ Adc	V(pk)	A(pk)	% / °C
1N6102A/US	6.12	175	5.2	500	10.5	142.8	.05
1N6103A/US	7.13	175	5.7	300	11.2	133.9	.06
1N6104A/US	7.79	150	6.2	100	12.1	124.0	.06
1N6105A/US	8.65	150	6.9	100	13.4	111.9	.06
1N6106A/US	9.50	125	7.6	100	14.5	103.4	.07
1N6107A/US	10.45	125	8.4	20	15.6	96.2	.07
1N6108A/US	11.40	100	9.1	20	16.9	88.8	.07
1N6109A/US	12.35	100	9.9	20	18.2	82.4	.08
1N6110A/US	14.25	75	11.4	20	21.0	71.4	.08
1N6111A/US	15.20	75	12.2	20	22.3	67.3	.08
1N6112A/US	17.10	65	13.7	10	25.1	59.8	.085
1N6113A/US	19.00	65	15.2	5.0	27.7	54.2	.085
1N6114A/US	20.9	50	16.7	5.0	30.5	49.2	.085
1N6115A/US	22.8	50	18.2	5.0	33.3	45.0	.09
1N6116A/US	25.7	50	20.6	5.0	37.4	40.1	.09
1N6117A/US	28.5	40	22.8	5.0	41.6	36.0	.09
1N6118A/US	31.4	40	25.1	5.0	45.7	32.8	.095
1N6119A/US	34.2	30	27.4	5.0	49.9	30.1	.095
1N6120A/US	37.1	30	29.7	5.0	53.6	28.0	.095
1N6121A/US	40.9	30	32.7	5.0	59.1	25.4	.095
1N6122A/US	44.7	25	35.8	5.0	64.6	23.2	.095
1N6123A/US	48.5	25	38.8	5.0	70.1	21.4	.095
1N6124A/US	53.2	20	42.6	5.0	77.0	19.5	.095
1N6125A/US	58.9	20	47.1	5.0	85.3	17.6	.100
1N6126A/US	64.6	20	51.7	5.0	97.1	15.4	.100
1N6127A/US	71.3	20	56.0	5.0	103.1	14.5	.100
1N6128A/US	77.9	15	62.2	5.0	112.8	13.3	.100
1N6129A/US	86.5	15	69.2	5.0	125.1	12.0	.100
1N6130A/US	95.0	12	76.0	5.0	137.6	10.9	.100
1N6131A/US	104.5	12	83.6	5.0	151.3	9.9	.100
1N6132A/US	114.0	10	91.2	5.0	165.1	9.1	.100
1N6133A/US	123.5	10	98.8	5.0	178.8	8.4	.105
1N6134A/US	142.5	8.0	114.0	5.0	206.3	7.3	.105
1N6135A/US	152	8.0	121.6	5.0	218.4	6.9	.105
1N6136A/US	171	5.0	136.8	5.0	245.7	6.1	.110
1N6137A/US	190	5.0	152.0	5.0	273.0	5.5	.110

- 221 West Industry Court ■ Deer Park, NY 11729-4681 ■ Phone (631) 586 7600 Fax (631) 242 9798 •
- World Wide Web Site - <http://www.sensitron.com> • E-Mail Address - sales@sensitron.com •

TECHNICAL DATA
DATA SHEET 5073, REV. -


MECHANICAL DIMENSIONS In Inches / (mm)

AXIAL



PACKAGE STYLE	DIMENSIONS - INCHES / MILLIMETERS			
	ϕB	ϕD	G	L
AXIAL	.026/.033	.085/.140	.140/.185	1.00/1.30
	.66/.84	2.16/3.56	3.56/4.70	25.4/33.02

MELF



R = 0.020 Max

STYLE	A	B	C	D
MELF	.200/.225	.019/.028	.003MIN	.137/.148
	5.08/5.72	.48/.71	.08MIN	3.48/3.76

SENSITRON **SEMICONDUCTOR**

SS6102A/US thru SS6137A/US

TECHNICAL DATA **DATA SHEET 5073, REV. –**

DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the Sensitron Semiconductor sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall Sensitron Semiconductor be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). Sensitron Semiconductor assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall Sensitron Semiconductor be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or Sensitron Semiconductor.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of Sensitron Semiconductor.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations.