



Pushing Performance
Since 1945

M12 PFT SD female A-cod 8-pol crimpflang



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 821 2827
Specification	M12 PFT SD female A-cod 8-pol crimpflang
HARTING eCatalogue	https://b2b.harting.com/21038212827

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design PushPull
Element	Cable connector Panel feed through
Specification	for rear mounting

Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded Shield connection with crimp flange
Number of contacts	8
Coding	A-coding
Locking type	Screw locking PushPull
Details	Please order crimp contacts separately. Please order crimp flange set separately.

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm ²
Conductor cross-section	AWG 26 ... AWG 22
Wire outer diameter	≤1.65 mm
Rated current	2 A



Pushing Performance
Since 1945

Technical characteristics

Rated voltage	30 V AC
	30 V DC
Rated impulse voltage	0.8 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	2 Nm Lock nut
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)



Pushing Performance
Since 1945

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	40 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140225718
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)