

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Wire guard: Stainless steel
- Item ③ Terminal Body(contact pin): Copper.Tin platd
- Item ④ Insulator(Cover): Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

- Electrical:
- | | | |
|--------------------------|------------------|------------------------|
| | cULus | IEC |
| ● Voltage rating: | 600V | 1000V |
| ● Current rating: | 37A | 76A |
| ● Wire range: | | 0.2-16 mm ² |
| ● Solid wire(AWG): | 6-24 | |
| ● Stranded wire(AWG): | 6-24 | |
| ● Wire strip length: | 12-13mm | |
| ● Withstanding Voltage: | 2.2KV | 8KV |
| ● Operating temperature: | -40°C to +115°C | |
| ● Soldering temperature: | 250°C±10°C/5 Sec | |
| ● Safety Approval: | | |





H8 xx 1 0 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
:
08: 8POLES

COLOR
0: BLACK
5: GREEN
6: BLUE
8: GREY

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.



PCB Layout

POLE		2	3	4	5	6	7	8
A		25.00	40.00	55.00	70.00	85.00	100.00	115.00
B		15.00	30.00	45.00	60.00	75.00	90.00	105.00
Tol.	±0.15				±0.25			
POLE	9	10	11	12	13	14	15	16
A	130.00	145.00	160.00	175.00	190.00	205.00	220.00	235.00
B	120.00	135.00	150.00	165.00	180.00	195.00	210.00	225.00
Tol.	±0.35				±0.50			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H8 15.0mm Series				DWG NO.	8H80002		
PART NO.	H8xx10x0xxxxG				DWG NO.	8H80002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance
		Runner 2010.10.15	Tony 2007.06.21					X. ±0.50
								X.X ±0.30
								X.XX ±0.10
								X° ±1°

UNIT: mm

SCALE: NONE

SHEET: 01/01

REV.: B