

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

1. PUSH-IN SAFETY SOCKET w/ $\varnothing$.080 ($\varnothing$ 2.0) SOLDER FORK.
2. SPECIFICATIONS:
INSULATOR: POLYAMIDE (NYLON)
CONTACT: BRASS, NICKEL PLATED
3. RATING:
VOLTAGE: 1,000V CATIII P2 (IEC61010-1)
CURRENT: 25A MAX.
RESISTANCE: $<5\text{m}\Omega$.
TEMPERATURE: -20°C TO $+80^{\circ}\text{C}$.
4. MOUNTING HOLE: REF. DIAGRAM.


PART NUMBER

CT2245-#


COLOR: 0 - BLACK
1 - BROWN
2 - RED
3 - ORANGE
4 - YELLOW
5 - GREEN
6 - BLUE
7 - PURPLE
8 - GRAY
9 - WHITE

REVISIONS

REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/12/99	
A	REVISED CONFIGURATION & MATL. MOUNTING HOLE. NEW TOOLING.	4/18/04	



THIRD ANGLE PROJECTION



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
FRACTIONS DECIMALS
 $\pm 1/32$.XX $\pm .02$
XXX $\pm .005$
DO NOT SCALE DRAWING

MATERIAL

FINISH

NEXT ASSY

USED ON

APPLICATION

CONTRACT NO.

APPROVALS

DATE

DRAWN

WDH

7/12/99

CHECKED

ENGR.

DESIGN ACTIVITY

Cal Test Electronics

22820 Savi Ranch Parkway
Yorba Linda, CA 92887-4610

TITLE

**4mm PUSH-IN SAFETY SOCKET,
w/ $\varnothing$.080 SOLDER FORK**

SIZE
A

CAGE CODE

43F45

DWG. NO.

P224500

REV.

A

SCALE

1:1

SHEET

1 OF 1