




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- APPLICATION TOOLS - RT2HT
- MINIMUM LOOP TENSILE STRENGTH - 450 LBS. (2002 NEWTONS) WHEN TESTED ON A 3" MANDREL
- BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
- TOLERANCES:

.XXX = ± .010 [.25]	.XX = ± .02 [.5]
.X = ± .03 [.8]	ANGLES = ± 2°
- MATERIAL: 316 STAINLESS STEEL
- COATING - POLYESTER
COATING THICKNESS: .002 MIN. / .005 MAX. PER SIDE



SECTION A-A
SCALE 4:1

							TITLE							
							METAL LOCKING TIE SUPER HEAVY DUTY FULLY COATED							
							CUSTOMER DRAWING							
							ITEM REVISION NAME	N41201BS/04			A			
							DATASET FILE NAME	N41201BS_DC/04A						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]							
							.X ± .1 [2.54]	.XXX ± .005 [.127]	ANGLES ± 5°					
							.XX ± .01 [.25]							
									THIRD ANGLE PROJECTION					
									DRAWING NUMBER:					
									N41201BS_DC					
REV	DATE	BY	CHK	APR	DESCRIPTION			ECN	DRAWN BY	DATE	SCALE			
04A	4/13	JAMB	MIM	RGRO	UPDATE DRAWING TO MNEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO			SSECN01049	JMMR	2/12	EJD			
03A	2/12	MIM	RGRO	---	NOTE #3 - METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY			-----			2:1			
											SHT 1 OF 1			
											SIZE A			