

NOTES:

I. MATERIALS AND FINISHES:

HEX NUT	- BRASS, NICKEL PLATING
LOCK WASHER	- BRASS, NICKEL PLATING
BODY	- BRASS, NICKEL PLATING
CONTACT	- PHOSPHOR BRONZE, GOLD PLATING
INSULATOR	- PTFE, NATURAL


2. ELECTRICAL:

- A. IMPEDANCE: 75 OHM, NOMINAL
- B. FREQUENCY RANGE: 0-2 GHz
- C. D.W.V: 1500 VRMS, MIN.

3. MECHANICAL:

- A. DURABILITY: 500 CYCLES MIN.
- B. TEMPERATURE RANGE: -40°C TO +85°C

4. MAX. PANEL THICKNESS = 5 MM



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
 <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES
 ± 0.05mm ± 0.1mm ± 0.2mm ± 0.3mm ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL -	DRAWN M.ZHANG	DATE 17-Oct-14	TITLE TNC FEMALE TO FEMALE BULKHEAD ADAPTER	Amphenol Connex
	ENGINEER S.DUAN	DATE 17-Oct-14		
REFERENCE T7471BI-ND3G-75	APPROVED S.HSIEH	DATE 17-Oct-14	SCALE: 4.0:1.0 SHEET 3 OF 3	DRAWING NO. ITEM NO. PART NO. 122345
	CONFIGURATION LEVEL: □□□	CAD FILE		
FINISH		DWG SIZE B	REV A	