

AHC

High voltage 1/4" x 1-1/4" fast-acting ceramic tube fuse



Product features

- High voltage ceramic tube fuse
- Compact 3AB footprint:
1/4" x 1 1/4" (6.3 x 32 mm)
- Fast-acting performance
- 600 V rating
- Cartridge and axial lead versions available
- Very high interrupting ratings to help safely protect against dangerous high fault currents
- Fuse accessories (cartridge version):
HVP Panel mount fuse holder (480V)
HVI In-line fuse holder (600V)
S-8000 Panel mount fuse block (600V)
1Axxxx (up to 600V) fuse clips

Agency information

- cURus recognition file number:
E19180 Guide JDYX2 and JDYX8



Applications

- Industrial control panels
- Motor control - UL 508A panels
- Uninterruptible power supplies (UPS)
- Variable frequency drives
- Energy storage and battery systems
- High voltage power conversion

Environmental compliance



Ordering part number

	BK-AHC-V-5-R
Packaging prefix	
Family name	
Option code (V = leaded)	
Ampere rating	
RoHS compliance	

Packaging prefix

- **Blank**
5 pieces in tin case for AHC-XXX-R, 4 pieces in tin case for AHC-V-XXX-R
- **BK1-**
1000 pieces in polybag for AHC-XXX-R
- **BK-**
100 pieces in carton for AHC-XXX-R, AHC-V-XXX-R or AHC-V2-XXX-R
- **TR-**
500 pieces on reel for AHC-V-XXX-R

Option code

- **-V**
Axial leads with 38.1 mm length – copper tinned wire with nickel plated brass over caps
- **-V2**
Axial leads with 50.8 mm length – copper tinned wire with nickel plated brass over caps



Powering Business Worldwide

Electrical characteristics

Amp Rating	1.0 In minimum	2.5 In maximum
0.2 A - 10 A	4 hours	120 seconds


Product specifications

Part number	Current rating (A)	Voltage rating (Vac)	Voltage rating (Vdc)	Interrupting rating @ rated voltage (A) Vac	Interrupting rating @ rated voltage (A) Vdc	Typical resistance ¹ (mΩ)	Typical voltage drop ² (mV)
AHC-200(-V)-R	0.2	600	600	10,000	10,000	4310	1060
AHC-250(-V)-R	0.25	600	600	10,000	10,000	2703	895
AHC-400(-V)-R	0.4	600	600	10,000	10,000	1436	730
AHC-500(-V)-R	0.5	600	600	10,000	10,000	1047.5	680
AHC-600(-V)-R	0.6	600	600	10,000	10,000	784.5	585
AHC-1(-V)-R	1	600	600	10,000	10,000	360	425
AHC-1-5(-V)-R	1.5	600	600	10,000	10,000	250	550
AHC-1-6(-V)-R	1.6	600	600	10,000	10,000	196	425
AHC-2(-V)-R	2.0	600	600	10,000	10,000	162	500
AHC-2-5(-V)-R	2.5	600	600	10,000	10,000	119	475
AHC-3(-V)-R	3.0	600	600	10,000	10,000	95	450
AHC-3-15(-V)-R	3.15	600	600	10,000	10,000	83	400
AHC-4(-V)-R	4.0	600	600	10,000	10,000	53.8	350
AHC-5(-V)-R	5.0	600	600	10,000	10,000	42.5	350
AHC-6(-V)-R	6.0	600	600	10,000	10,000	30.3	250
AHC-8(-V)-R	8.0	600	600	10,000	10,000	23	300
AHC-10(-V)-R	10	600	-	10,000	10,000	16.5	300

1. Typical resistance measured at <10% of rated current at +23 °C
2. Typical melting I²t measured at 10x of rated current
3. Typical voltage drop measured at +23 °C and rated current

Dimensions- mm

Drawing not to scale




Dimension	Value (mm)
A	31.75 ± 0.8
B	6.35 ± 0.1
C	32.72 ± 0.8
E	6.98 ± 0.3
F	0.8 ± 0.05
G	4.8 +0.4/-0.0

Part number	Dimension D
AHC-V-XXX-R	38.1 mm (REF)
BK-AHC-V-XXX-R	38.1 mm (REF)
BK-AHC-V2-XXX-R	50.8 mm (REF)
TR-AHC-V-XXX-R	20 mm (REF)


General specifications

Operating temperature: -55 °C to +125 °C with proper correction factor applied
Terminal strength: MIL-STD-202G, Method 211A, Test condition A, Pull force 10N/10S
Thermal shock: MIL-STD-202, Method 107G: -55 °C to +125 °C, 5 cycles
Mechanical shock: MIL-STD-202 Method 213. Condition A: Half-sine shock pulse, peak=50 g's, 11 ms, total 18 shocks
Vibration: According to IEC60068-2-6: The specimens shall be subjected to a simple harmonic motion having an amplitude of 0.03 inch (0.06 inch maximum total excursion), the frequency being varied uniformly between the approximate limits of 10 and 55 hertz (Hz). The entire frequency range, from 10 to 55 Hz and return to 10 Hz, shall be traversed in approximately 1 minute.
Humidity: MIL-STD-202G, Method 103B, Test condition A: 95% RH, +40 °C, 240 hours
Solderability: IEC-60127-2, A.3.3: No steam ageing. Immersion conditions: +250 °C +/-3 °C, 3s +/-0.3s


Temperature derating curve




Time vs. current curve




I²t vs. current



I²t vs. time curve



Wave solder profile (Axial lead only)



Reference EN 61760-1:2006

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat		
• Temperature min. (T_{smin})	100 °C	100 °C
• Temperature typ. (T_{styp})	120 °C	120 °C
• Temperature max. (T_{smax})	130 °C	130 °C
• Time (T_{smin} to T_{smax}) (t_s)	70 seconds	70 seconds
Δ preheat to max Temperature	150 °C max.	150 °C max.
Peak temperature (T_p)*	235 °C – 260 °C	250 °C – 260 °C
Time at peak temperature (t_p)	10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave
Ramp-down rate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max
Time 25 °C to 25 °C	4 minutes	4 minutes

Manual solder

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2023 Eaton
All Rights Reserved
Printed in USA
Publication No. ELX1121
February 2023

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.

Follow us on social media to get the
latest product and support information.

