



PRODUCT NUMBER	PITCH
VZxx30x000J0G	3.81 mm





DIMENSION

Dim A	N×3.81+14.39
Dim B	(N-1)×3.81
Dim C	(N-1)×3.81+10.0
Dim D	(N-1)×3.81+13.95
Dim E	(N-1)×3.81
Dim F	(N-1)×3.81+4.54
N=Number of poles	
Poles	Tolerance
2-5P	±0.20
6-10P	±0.30
11-15P	±0.35
16-24P	±0.40

PART NO.: VZ xx 30 x 0 00J0 G

Solid block	No. of poles	Color	RoHS compliant
0	2	Black (RAL9005)	In copper Alloy
02	2 poles	Red (RAL3001/D)	
03	3 poles	Orange(RAL2011/P)	
...	...	Yellow(RAL1018/A)	
...	...	Green(RAL6018/T)	
24	24 poles	Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

RECOMMENDED P.C.B CUTOUT
TOP VIEW

Material:

- Item(a) Solder Pin: Brass with Tin plated
- Item(b) Flange nut: brass M2.5
- Item(c) Terminal (housing): Thermoplastic(UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family	
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK	
					angles		title	
					0.1°		TERMINAL BLOCK	
					X'±1°		PLUGGABLE SOCKET, FEED-THROUGH HEADER	
					dr	EVIN ZHONG 050714	dwg no	
					enrg	EVIN ZHONG 050714	sheet 1 of 1 size	
					chr	HANKE FENG 050714	VZxx30x000J0G	
					appd	SHI JUN 050714	type	
							CUSTOMER Drawing	
sheet index	revision	A						
	sheet	1						