




PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C4GV00LF	D09P91C6GV00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C4GV00LF	D15P91C6GV00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C4GV00LF	D25P91C6GV00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C4GV00LF	D37P91C6GV00LF
						200 Matings	500 Matings

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
B	-	PES	1996/07/24	angles	linear	.0±0.1		scale 2:1		MALE DELTA D CONNECTOR EUROPE STRAIGHT PRESS FIT			
C	LS05-004	MPE	2005-02-10			.00±0.1							
D	LS06-0097	LGO	2006-07-29			.000±0.1							
E	LS06-0186	LGO	2006-07-29	dr	PESSON		1995-08-25		Amphenol FCi	dwg no		sheet 1 of 1	size
F	111-0062	RPK	2011-04-05	engr	MITHUN PAUL		2016-06-06			C01-8646-0360		A3	
G	ELX-I-24020	AAB	2016-06-06	chr	ATHUL A.B		2016-06-06			type		Product Customer Drawing	
				appd	BIJU K PAUL		2016-06-06						
sheet index		revision sheet		G	1								