




Product: [RKUE 19-242](#) 

M23 - Female 0° | #Contacts: 19 (18+PE)| 120 V | Cable: Black (PUR); 16x0.5 mm² + 3x1.0 mm²; IEC

Product Description

M23 - Singled-Ended Female Straight Cordset | #Contacts: 19 (18+PE) | 120 V / 16x8 A + 3x10 A | Grey PUR Jacket, 16x0.5 mm² (20 AWG) + 3x1.0 mm² (17 AWG), IEC

Technical Drawing



Technical Specifications

Face View

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5	Pin 6	Pin 7	Pin 8	Pin 9	Pin 10	Pin 11	Pin 12	Pin 13	Pin 14	Pin 15	Pin 16	Pin 17	Pin 18	Pin 19
violet	red	grey	red-blue	green	blue	grey-pink	white-green	white-yellow	white-grey	black	green-yellow	yellow-brown	brown-green	white	yellow	pink	grey-brown	brown

Technical Data

Product Family:	Power Connector
Side 1 Product Sub Family:	M23 Power
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Side 1 Type of Contact/Gender:	Socket Contact / Female
Connector Design:	M23 Female 19 Pole 0°
Number of Pins:	19 (18+PE)
Shielding Type:	Unshielded
Attachment Type:	Grounded Coupling Nut
Voltage Rating:	125 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	120 V AC/DC
Current Rating:	16 x 8 A (pin-Ø 1 mm), 2 x 10 A (contact-Ø 1.5 mm)
Insulation Resistance:	> 10 ⁹ Ohm
Mating Cycles:	≤ 100

Cross Section:	16x0.5mm² + 3x1.0 mm²
Ambient Temperature (Operation)*:	- 25 °C to + 80 °C
Protection Degree / IP Rating**:	IP67
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Clearance / Creepage Distance:	acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	II acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	Brass (CuZn)
Side 1 Contact Plating:	Gold over Copper (Cu/Au)
Contact Bearer Material:	Polyamide (Nylon), PA 6.6
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 V0
Molded Body Material:	Thermoplastic Polyurethane (TPU)
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94-HB
Attachment Material:	Brass (CuZn)
Attachment Plating:	Nickel (Ni)
O-Ring Material:	Nitrile Butadiene Rubber (NBR)

Cable Data

Cable Number:	242
Conductor Size:	16x0.5mm² + 3x1.0 mm²
Number of Wires:	19
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 2 M
Conductor Material:	Cu
Cable Jacket Material:	Polyurethane (PUR)
Cable Jacket Color:	Black
Cable Diameter D:	Ø 11.60
Wire Insulation Material:	Polypropylene (PP)
Insulated Wire Diameter:	16 x Ø 1.45 mm + 3 x Ø 1.95 mm
Ambient Temperature (Fixed Installation):	- 50 °C to + 80 °C
Ambient Temperature (Flex Installation):	- 25 °C to + 80 °C
Ambient Temperature (Drag Chain Inst):	max. + 60 °C
UL Cable Type:	AWM: 21198 / 20549
Flammability Class (Cable Jacket):	IEC 60332-2, VDE 0482-265-2-2, EN 50265-2-2, FT2; flame-retardant
Cable Characteristics:	Flexibility: Excellent Abrasion Resistance: Excellent Oil & Chemical Resistance: Excellent UV Resistance: Excellent Low Temp Performance: Excellent (flexible to -40°C) Flame Retardance: Good Halogen-Free: Yes Mechanical Durability: Excellent (resists impact, tear, and flex) Drag Chain Environmental Suitability: Outdoor, oily, wet, or rough environments

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Halogenfree:	IEC 60754-1, VDE 0482-267, EN 50267-2-1
--------------	---

Notes

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
Note:	Do not connect / disconnect under load.

Particularities:	When the connector is unlocked and in risk of pollution the connector has to be covered with a protective cap $\geq$ IP54.
------------------	--

Variants

Item #	Item Description	Cable Length
18337	RKUE 19-242/110 M	
1504	RKUE 19-242/1 M	1 m
91506	RKUE 19-242/3 M	3 m
60710	RKUE 19-242/5 M	5 m
60707	RKUE 19-242/10 M	10 m
60708	RKUE 19-242/15 M	15 m
60709	RKUE 19-242/20 M	20 m
61245	RKUE 19-242/25 M	25 m
61244	RKUE 19-242/30 M	30 m
934637368	RKUE 19-242/35 M	35 m
75635	RKUE 19-242/40 M	40 m
70977	RKUE 19-242/50 M	50 m
75646	RKUE 19-242/60 M	60 m
75647	RKUE 19-242/70 M	70 m
75648	RKUE 19-242/80 M	80 m

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.