


**INSULATED GATE BIPOLAR TRANSISTOR WITH ULTRA-FAST  
SOFT RECOVERY DIODE**

**Features**


- Low  $V_{CE(ON)}$  Non Punch Through IGBT technology
- Low Diode  $V_F$
- 10 $\mu$ s Short Circuit Capability
- Square RBSOA
- Ultra-soft Diode Reverse Recovery Characteristics
- Positive  $V_{CE(ON)}$  temperature co-efficient
- Lead-free

**Benefits**

- Benchmark Efficiency for Motor Control
- Rugged transient performance for increased reliability
- Excellent current sharing in parallel operation
- Low EMI



$V_{CES} = 600V$   
 $I_C = 3.7A, T_C = 100^\circ C$   
 $T_{J(MAX)} = 150^\circ C$   
 $V_{CE(ON)} \text{ typ.} = 1.95V$



|      |           |         |
|------|-----------|---------|
| G    | C         | E       |
| Gate | Collector | Emitter |

| Base part number | Package Type | Standard Pack       |          | Orderable Part Number |
|------------------|--------------|---------------------|----------|-----------------------|
|                  |              | Form                | Quantity |                       |
| IRGR2B60KDPbF    | D-Pak        | Tube                | 75       | IRGR2B60KDPbF         |
|                  |              | Tape and Reel       | 2000     | IRGR2B60KDTRPbF       |
|                  |              | Tape and Reel Left  | 3000     | IRGR2B60KDTRLpF       |
|                  |              | Tape and Reel Right | 3000     | IRGR2B60KDTRRpF       |

**Absolute Maximum Ratings**

|                           | Parameter                                        | Max.                                | Units      |
|---------------------------|--------------------------------------------------|-------------------------------------|------------|
| $V_{CES}$                 | Collector-to-Emitter Voltage                     | 600                                 | V          |
| $I_C @ T_C = 25^\circ C$  | Continuous Collector Current                     | 6.3                                 | A          |
| $I_C @ T_C = 100^\circ C$ | Continuous Collector Current                     | 3.7                                 |            |
| $I_{CM}$                  | Pulse Collector Current, $V_{GE} = 15V$ ② ⑤      | 8.0                                 |            |
| $I_{LM}$                  | Clamped Inductive Load Current, $V_{GE} = 20V$ ① | 8.0                                 |            |
| $I_F @ T_C = 25^\circ C$  | Diode Continuous Forward Current                 | 6.3                                 |            |
| $I_F @ T_C = 100^\circ C$ | Diode Continuous Forward Current                 | 3.7                                 |            |
| $I_{FM}$                  | Diode Maximum Forward Current ②                  | 8.0                                 |            |
| $V_{GE}$                  | Continuous Gate-to-Emitter Voltage               | $\pm 20$                            | V          |
| $P_D @ T_C = 25^\circ C$  | Maximum Power Dissipation                        | 35                                  | W          |
| $P_D @ T_C = 100^\circ C$ | Maximum Power Dissipation                        | 14                                  |            |
| $T_J$                     | Operating Junction and                           | -55 to +150                         | $^\circ C$ |
| $T_{STG}$                 | Storage Temperature Range                        |                                     |            |
|                           | Soldering Temperature, for 10 sec.               | 300<br>(0.063 in.(1.6mm) from case) |            |

**Thermal Resistance**

|                         | Parameter                         | Min. | Typ. | Max. | Units        |
|-------------------------|-----------------------------------|------|------|------|--------------|
| $R_{\theta JC}$ (IGBT)  | Junction-to-Case (IGBT) ④         | —    | —    | 3.56 | $^\circ C/W$ |
| $R_{\theta JC}$ (Diode) | Junction-to-Case (Diode) ④        | —    | —    | 7.70 |              |
| $R_{\theta JA}$         | Junction-to-Ambient (PCB Mount) ⑥ | —    | —    | 50   |              |

**Electrical Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**


|                                 | Parameter                               | Min. | Typ. | Max. | Units   | Conditions                                            |
|---------------------------------|-----------------------------------------|------|------|------|---------|-------------------------------------------------------|
| $V_{(BR)CES}$                   | Collector-to-Emitter Breakdown Voltage  | 600  | —    | —    | V       | $V_{GE} = 0V, I_C = 500\mu A$ ③                       |
| $\Delta V_{(BR)CES}/\Delta T_J$ | Temperature Coeff. of Breakdown Voltage | —    | 0.49 | —    | V/°C    | $V_{GE} = 0V, I_C = 1mA$ (25°C-150°C)                 |
| $V_{CE(on)}$                    | Collector-to-Emitter Saturation Voltage | —    | 1.95 | 2.25 | V       | $I_C = 2.0A, V_{GE} = 15V, T_J = 25^\circ\text{C}$    |
|                                 |                                         | —    | 2.28 | —    |         | $I_C = 2.0A, V_{GE} = 15V, T_J = 150^\circ\text{C}$   |
| $V_{GE(th)}$                    | Gate Threshold Voltage                  | 4.0  | —    | 6.0  | V       | $V_{CE} = V_{GE}, I_C = 250\mu A$                     |
| $g_{fe}$                        | Forward Transconductance                | —    | 1.2  | —    | S       | $V_{CE} = 50V, I_C = 2.0A, PW = 20\mu s$              |
| $I_{CES}$                       | Collector-to-Emitter Leakage Current    | —    | 0.5  | 25   | $\mu A$ | $V_{GE} = 0V, V_{CE} = 600V$                          |
|                                 |                                         | —    | 23   | —    |         | $V_{GE} = 0V, V_{CE} = 600V, T_J = 150^\circ\text{C}$ |
| $V_{FM}$                        | Diode Forward Voltage Drop              | —    | 1.3  | 1.6  | V       | $I_F = 2.0A$                                          |
|                                 |                                         | —    | 1.1  | —    |         | $I_F = 2.0A, T_J = 150^\circ\text{C}$                 |
| $I_{GES}$                       | Gate-to-Emitter Leakage Current         | —    | —    | ±100 | nA      | $V_{GE} = \pm 20V$                                    |

**Switching Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**


|              | Parameter                            | Min.        | Typ. | Max. | Units   | Conditions                                                                                                                                                |
|--------------|--------------------------------------|-------------|------|------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| $Q_g$        | Total Gate Charge (turn-on)          | —           | 8.0  | 12   | nC      | $I_C = 2.0A$<br>$V_{GE} = 15V$<br>$V_{CC} = 400V$                                                                                                         |
| $Q_{ge}$     | Gate-to-Emitter Charge (turn-on)     | —           | 1.3  | 2.0  |         |                                                                                                                                                           |
| $Q_{gc}$     | Gate-to-Collector Charge (turn-on)   | —           | 4.0  | 6.0  |         |                                                                                                                                                           |
| $E_{on}$     | Turn-On Switching Loss               | —           | 74   | 160  | $\mu J$ | $I_C = 2.0A, V_{CC} = 400V, V_{GE} = 15V$<br>$R_G = 100\Omega, L = 7.1mH, T_J = 25^\circ\text{C}$<br>Energy losses include tail & diode reverse recovery  |
| $E_{off}$    | Turn-Off Switching Loss              | —           | 39   | 120  |         |                                                                                                                                                           |
| $E_{tot}$    | Total Switching Loss                 | —           | 113  | 280  |         |                                                                                                                                                           |
| $t_{d(on)}$  | Turn-On delay time                   | —           | 11   | 30   | ns      | Energy losses include tail & diode reverse recovery                                                                                                       |
| $t_r$        | Rise time                            | —           | 8.7  | 25   |         |                                                                                                                                                           |
| $t_{d(off)}$ | Turn-Off delay time                  | —           | 150  | 170  |         |                                                                                                                                                           |
| $t_f$        | Fall time                            | —           | 56   | 75   |         |                                                                                                                                                           |
| $E_{on}$     | Turn-On Switching Loss               | —           | 120  | —    | $\mu J$ | $I_C = 2.0A, V_{CC} = 400V, V_{GE} = 15V$<br>$R_G = 100\Omega, L = 7.1mH, T_J = 150^\circ\text{C}$<br>Energy losses include tail & diode reverse recovery |
| $E_{off}$    | Turn-Off Switching Loss              | —           | 68   | —    |         |                                                                                                                                                           |
| $E_{tot}$    | Total Switching Loss                 | —           | 188  | —    |         |                                                                                                                                                           |
| $t_{d(on)}$  | Turn-On delay time                   | —           | 13   | —    | ns      | Energy losses include tail & diode reverse recovery                                                                                                       |
| $t_r$        | Rise time                            | —           | 6.8  | —    |         |                                                                                                                                                           |
| $t_{d(off)}$ | Turn-Off delay time                  | —           | 170  | —    |         |                                                                                                                                                           |
| $t_f$        | Fall time                            | —           | 110  | —    |         |                                                                                                                                                           |
| $C_{ies}$    | Input Capacitance                    | —           | 110  | —    | pF      | $V_{GE} = 0V$<br>$V_{CC} = 30V$<br>$f = 1.0MHz$                                                                                                           |
| $C_{oes}$    | Output Capacitance                   | —           | 17   | —    |         |                                                                                                                                                           |
| $C_{res}$    | Reverse Transfer Capacitance         | —           | 4.0  | —    |         |                                                                                                                                                           |
| RBSOA        | Reverse Bias Safe Operating Area     | FULL SQUARE |      |      |         | $T_J = 150^\circ\text{C}, I_C = 8.0A$<br>$V_{CC} = 480V, V_p \leq 600V$<br>$R_g = 100\Omega, V_{GE} = +20V$ to 0V                                         |
| SCSOA        | Short Circuit Safe Operating Area    | 10          | —    | —    | $\mu s$ | $T_J = 150^\circ\text{C}, V_p \leq 600V, R_g = 330\Omega$<br>$V_{CC} = 360V, V_{GE} = +15V$ to 0V                                                         |
| $E_{rec}$    | Reverse Recovery Energy of the Diode | —           | 19   | 30   | $\mu J$ | $T_J = 150^\circ\text{C}$                                                                                                                                 |
| $t_{rr}$     | Diode Reverse Recovery Time          | —           | 45   | 68   | ns      | $V_{CC} = 400V, I_F = 2.0A, L = 7.1mH$                                                                                                                    |
| $I_{rr}$     | Diode Peak Reverse Recovery Current  | —           | 5.8  | 8.7  | A       | $V_{GE} = 15V, R_g = 100\Omega$                                                                                                                           |

**Notes:**


- ①  $V_{CC} = 80\% (V_{CES}), V_{GE} = 20V, L = 200\mu H, R_G = 100\Omega$ .
- ② Pulse width limited by max. junction temperature.
- ③ Refer to AN-1086 for guidelines for measuring  $V_{(BR)CES}$  safely.
- ④  $R_\theta$  is measured at  $T_J$  of approximately 90°C.
- ⑤ FBSOA operating conditions only.
- ⑥ When mounted on 1" square PCB (FR-4 or G-10 Material). For recommended footprint and soldering techniques refer to application note #AN-994.




**Fig. 1 - Typical Load Current vs. Frequency**  
(Load Current =  $I_{\text{RMS}}$  of fundamental)




**Fig. 2 - Maximum DC Collector Current vs. Case Temperature**




**Fig. 3 - Power Dissipation vs. Case Temperature**




**Fig. 4 - Forward SOA**  
 $T_c = 25^{\circ}\text{C}$ ;  $T_j \leq 150^{\circ}\text{C}$ ;  $V_{\text{GE}} = 15\text{V}$




**Fig. 5 - Reverse Bias SOA**  
 $T_j = 150^{\circ}\text{C}$ ;  $V_{\text{GE}} = 20\text{V}$




**Fig. 6** - Typ. IGBT Output Characteristics  
 $T_J = -40^{\circ}\text{C}$ ;  $t_p = 20\mu\text{s}$




**Fig. 7** - Typ. IGBT Output Characteristics  
 $T_J = 25^{\circ}\text{C}$ ;  $t_p = 20\mu\text{s}$




**Fig. 8** - Typ. IGBT Output Characteristics  
 $T_J = 150^{\circ}\text{C}$ ;  $t_p = 20\mu\text{s}$




**Fig. 9** - Typ. Diode Forward Voltage Drop Characteristics




**Fig. 10** - Typical  $V_{CE}$  vs.  $V_{GE}$   
 $T_J = -40^{\circ}\text{C}$




**Fig. 11** - Typical  $V_{CE}$  vs.  $V_{GE}$   
 $T_J = 25^{\circ}\text{C}$



**Fig. 12** - Typical  $V_{CE}$  vs.  $V_{GE}$   
 $T_J = 150^\circ\text{C}$




**Fig. 13** - Typ. Transfer Characteristics  
 $V_{CE} = 50\text{V}$ ;  $t_p = 20\mu\text{s}$




**Fig. 14** - Typ. Energy Loss vs.  $I_C$

$T_J = 150^\circ\text{C}$ ;  $L = 7.1\text{mH}$ ;  $V_{CE} = 400\text{V}$ ;  $R_G = 100\Omega$ ;  $V_{GE} = 15\text{V}$




**Fig. 15** - Typ. Switching Time vs.  $I_C$

$T_J = 150^\circ\text{C}$ ;  $L = 7.1\text{mH}$ ;  $V_{CE} = 400\text{V}$ ;  $R_G = 100\Omega$ ;  $V_{GE} = 15\text{V}$




**Fig. 16** - Typ. Energy Loss vs.  $R_G$

$T_J = 150^\circ\text{C}$ ;  $L = 7.1\text{mH}$ ;  $V_{CE} = 400\text{V}$ ;  $I_{CE} = 2.0\text{A}$ ;  $V_{GE} = 15\text{V}$




**Fig. 17** - Typ. Switching Time vs.  $R_G$


$T_J = 150^\circ\text{C}$ ;  $L = 7.1\text{mH}$ ;  $V_{CE} = 400\text{V}$ ;  $I_{CE} = 2.0\text{A}$ ;  $V_{GE} = 15\text{V}$




**Fig. 18** - Typical Diode  $I_{RR}$  vs.  $I_F$   
 $T_J = 150^\circ\text{C}$




**Fig. 19** - Typical Diode  $I_{RR}$  vs.  $R_G$   
 $T_J = 150^\circ\text{C}; I_F = 2.0\text{A}$




**Fig. 20** - Typical Diode  $I_{RR}$  vs.  $di_F/dt$   
 $V_{CC} = 400\text{V}; V_{GE} = 15\text{V}; I_F = 2.0\text{A}; T_J = 150^\circ\text{C}$




**Fig. 21** - Typical Diode  $Q_{RR}$   
 $V_{CC} = 400\text{V}; V_{GE} = 15\text{V}; T_J = 150^\circ\text{C}$




**Fig. 22** - Typ. Diode  $E_{RR}$  vs.  $I_F$   
 $T_J = 150^\circ\text{C}$




**Fig. 23** - Typ. Capacitance vs.  $V_{CE}$   
 $V_{GE} = 0\text{V}; f = 1\text{MHz}$








**Fig. 23 - Typical Gate Charge vs.  $V_{GE}$**   
 $I_{CE} = 2.0A$




**Fig. 24 - Maximum Transient Thermal Impedance, Junction-to-Case (IGBT)**




**Fig. 25 - Maximum Transient Thermal Impedance, Junction-to-Case (DIODE)**



**Fig.C.T.1** - Gate Charge Circuit (turn-off)

**Fig.C.T.2** - RBSOA Circuit

**Fig.C.T.3** - S.C. SOA Circuit

**Fig.C.T.4** - Switching Loss Circuit

**Fig. C.T.5** - Resistive Load Circuit




**Fig. WF1** - Typ. Turn-off Loss Waveform  
@  $T_J = 150^{\circ}\text{C}$  using Fig. CT.4



**Fig. WF2** - Typ. Turn-on Loss Waveform  
@  $T_J = 150^{\circ}\text{C}$  using Fig. CT.4




**Fig. WF3** - Typ. Diode Recovery Waveform  
@  $T_J = 150^{\circ}\text{C}$  using Fig. CT.4



**Fig. WF4** - Typ. S.C. Waveform  
@  $T_J = 150^{\circ}\text{C}$  using Fig. CT.3

# D-Pak (TO-252AA) Package Outline

Dimensions are shown in millimeters (inches)



## NOTES:

- 1.- DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
- 2.- DIMENSIONS ARE SHOWN IN INCHES [MILLIMETERS]
- 3.- LEAD DIMENSION UNCONTROLLED IN L5.
- 4.- DIMENSION D1, E1, L3 & b3 ESTABLISH A MINIMUM MOUNTING SURFACE FOR THERMAL PAD.
- 5.- SECTION C-C DIMENSIONS APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN .005 AND 0.10 [0.13 AND 0.25] FROM THE LEAD TIP.
- 6.- DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005 [0.13] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
- 7.- DIMENSION b1 & c1 APPLIED TO BASE METAL ONLY.
- 8.- DATUM A & B TO BE DETERMINED AT DATUM PLANE H.
- 9.- OUTLINE CONFORMS TO JEDEC OUTLINE TO-252AA.

| S<br>Y<br>M<br>B<br>O<br>L | DIMENSIONS  |       |           |      | N<br>O<br>T<br>E<br>S |
|----------------------------|-------------|-------|-----------|------|-----------------------|
|                            | MILLIMETERS |       | INCHES    |      |                       |
|                            | MIN.        | MAX.  | MIN.      | MAX. |                       |
| A                          | 2.18        | 2.39  | .086      | .094 | 7                     |
| A1                         | —           | 0.13  | —         | .005 |                       |
| b                          | 0.64        | 0.89  | .025      | .035 |                       |
| b1                         | 0.65        | 0.79  | .025      | .031 | 4                     |
| b2                         | 0.76        | 1.14  | .030      | .045 |                       |
| b3                         | 4.95        | 5.46  | .195      | .215 |                       |
| c                          | 0.46        | 0.61  | .018      | .024 | 7                     |
| c1                         | 0.41        | 0.56  | .016      | .022 |                       |
| c2                         | 0.46        | 0.89  | .018      | .035 |                       |
| D                          | 5.97        | 6.22  | .235      | .245 | 6                     |
| D1                         | 5.21        | —     | .205      | —    |                       |
| E                          | 6.35        | 6.73  | .250      | .265 | 4                     |
| E1                         | 4.32        | —     | .170      | —    |                       |
| e                          | 2.29 BSC    |       | .090 BSC  |      | 4                     |
| H                          | 9.40        | 10.41 | .370      | .410 |                       |
| L                          | 1.40        | 1.78  | .055      | .070 |                       |
| L1                         | 2.74 BSC    |       | .108 REF. |      | 3                     |
| L2                         | 0.51 BSC    |       | .020 BSC  |      |                       |
| L3                         | 0.89        | 1.27  | .035      | .050 |                       |
| L4                         | —           | 1.02  | —         | .040 | 3                     |
| L5                         | 1.14        | 1.52  | .045      | .060 |                       |
| ø                          | 0"          | 10"   | 0"        | 10"  |                       |
| ø1                         | 0"          | 15"   | 0"        | 15"  |                       |
| ø2                         | 25"         | 35"   | 25"       | 35"  |                       |

## LEAD ASSIGNMENTS

## HEXFET

- 1.- GATE
- 2.- DRAIN
- 3.- SOURCE
- 4.- DRAIN

## IGBT & CoPAK


- 1.- GATE
- 2.- COLLECTOR
- 3.- EMITTER
- 4.- COLLECTOR

# D-Pak (TO-252AA) Part Marking Information

EXAMPLE: THIS IS AN IRFR120  
WITH ASSEMBLY  
LOT CODE 1234  
ASSEMBLED ON WW 16, 1999  
IN THE ASSEMBLY LINE 'A'

INTERNATIONAL  
RECTIFIER  
LOGO

ASSEMBLY  
LOT CODE




PART NUMBER

DATE CODE  
YEAR 9 = 1999  
WEEK 16  
LINE A

Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>


# D-Pak (TO-252AA) Tape and Reel Information

Dimensions are shown in millimeters (inches)



## NOTES :

1. CONTROLLING DIMENSION : MILLIMETER.
2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS ( INCHES ).
3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



## NOTES :

1. OUTLINE CONFORMS TO EIA-481.

Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>

# Qualification Information<sup>†</sup>

|                            |                         |      |
|----------------------------|-------------------------|------|
| Qualification Level        | Industrial <sup>†</sup> |      |
| Moisture Sensitivity Level | D-Pak                   | MSL1 |
| RoHS Compliant             | Yes                     |      |

† Qualification standards can be found at International Rectifier's web site: <http://www.irf.com/product-info/reliability/>

†† Applicable version of JEDEC standard at the time of product release.

International  
 Rectifier

IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA

To contact International Rectifier, please visit <http://www.irf.com/whoto-call/>