


TROMPETER MODEL NO.	"A"	Ø"B"
CBBJR79	.24	.063
CBBJR79A	.34	.070




REV	ECN	DATE
F	12905	8/12/1999
G	15785	2/22/2005
H	55208	11/3/2014





CBBJR79 SHOWN



RECOMMENDED MTG
HOLE PATTERN


NOTES: UNLESS OTHERWISE SPECIFIED:

1. MATERIAL & FINISH:
   1.1 BODY: TIN PLATED BRASS
   1.2 INSULATOR & DIELECTRIC: PTFE (TEFLON)
   1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
   1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
   1.5 MOUNTING HARDWARD: TIN PLATED COPPER ALLOY

2. ELECTRICAL:
   2.1 FREQUENCY (MAX): 500 MHz
   2.2 IMPEDANCE: NON-CONSTANT

3. PANEL NUT TORQUE (MAX): 35 INCH POUNDS

4. PANEL THCKNESS (MAX): .125



RECOMMENDED
PANEL CUTOUT

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018

Model No: CBBJR79X

RoHS2 ☑ 2015/863/EU

UNLESS OTHERWISE SPECIFIED UNITS: INCH
.XX ±.02
.XXX ±.010
ANGLES ±2°

Cage Code 14949

3RD ANGLE PROJECTION

ENGINEER: C.MONAHAN

Date: 4/14/2026

TROMPETER

Title: TRB JACK, CIRCUIT BOARD, RIGHT ANGLE

Drawing No. C_3-0235 REV. H

Size A | DO NOT SCALE DRAWING | Workmanship Std: TFS-4 | Sheet 1 OF 1

Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.