


COAXIAL CONNECTOR, QMA, 50 Ohm, Right angle PCB jack (female)
85_QMA-50-0-4/111_N

Properties

- Excellent electrical performance
- High packing density
- Applicable in frequencies up to 18 GHz
- Easy to mate - No torque or tooling required
- Return loss optimized DC to 6 GHz



Product configuration		
Interface type	Gender	Standard
QMA	jack	QMA QLF compliant

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Bronze	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.0047 kg
Mating cycles	100
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	9.7 mm
Height of stand off HS	0.5 mm

Environmental data	
Operation temperature	-40 °C ... 85 °C

COAXIAL CONNECTOR, QMA, 50 Ohm, Right angle PCB jack (female)
85_QMA-50-0-4/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23034059	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23034059	85_QMA-50-0-4/111_NH	Bulk 100 pcs

Additional Information	
Remarks	PCB connector with stand-offs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1274 / Date of publication: 12.07.2025 / uncontrolled copy