

JSOM-1524-02

JSOM-1524-02

## JSOM SERIES

# MICRO JACK SCREW STANDOFF

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?JSOM](http://www.samtec.com?JSOM)

**Material:**  
Stainless Steel

## ALSO AVAILABLE (MOQ Required)

- Other heights

Works with  
PCI/104-Express™  
systems

(15.24 mm) .600"  
stack height

INDUSTRY STANDARD	INTERCONNECTS			
	TERMINAL	SOCKET	BANKS	STACK HEIGHT
PCI/104-Express™	ASP-129637-03	ASP-129646-03	3	15.24 mm
PCI/104-Express™	ASP-129637-13	ASP-129646-22	1	15.24 mm
SUMIT™	ASP-129637-01	ASP-129646-01	1	15.24 mm

JSOM

BOARD  
STACKER

LEAD STYLE



**-1524**

= (15.24 mm) .600"  
Stack Height

**-02**

= Female Thread

## APPLICATION



Components are to be packaged in separate bags unassembled.