

Part Number : 2014510101
Product Description : 1.25mm Pitch SlimStack Floating Board-to-Board Receptacle, Surface Mount, Right-Angle, 4.20mm Stacking Height, 17.70mm Width, 10 Circuits
Series Number : 201451
Status : Obsolete
Product Category : Board-to-Board Connectors

Obsolete

Documents and Resources

Drawings

2014510101_sd.pdf

2014510101_stp.zip

Specifications

2014510000-004.pdf

2014510000-005.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Board-to-Board Connectors
Series	0.8 and above, FSR1
Description	1.25mm Pitch SlimStack Floating Board-to-Board Receptacle, Surface Mount, Right-Angle, 4.20mm Stacking Height, 17.70mm Width, 10 Circuits
Application	Board-to-Board
Component Type	Receptacle
Product Name	SlimStack
UPC	889056858618

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Guide to Mating Part	Yes
Mated Height	4.20mm
Mated Width	17.70mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin-Bismuth

Obsolete

Downloaded from Arrow.com.

Material - Plating Termination	Tin-Bismuth
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	803.630/mg
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.25mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch SlimStack Floating Board-to-Board Plugs	201452

Obsolete

Downloaded from Arrow.com.