

Part Number : [1719830142](#)

Product Description : Nano-Pitch I/O Connector, Vertical, Surface Mount, with Cap, 42 Circuits, Black

Series Number : 171983

Status : Obsolete

Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

[1719830142_sd.pdf](#)

[PK-171982-9000-001.pdf](#)

[PK-171983-9000-001.pdf](#)

[PK-173307-0001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[SYM-171983-0142-001.zip](#)

[EE-171983-0005-002.pdf](#)

[SP-171983-0005-001.zip](#)

Specifications

[AS-173162-0001-001.pdf](#)

[AS-173162-0002-001.pdf](#)

[PS-173162-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	High-Speed I/O Connectors
Series	171983
Description	Nano-Pitch I/O Connector, Vertical, Surface Mount, with Cap, 42 Circuits, Black
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Nano-Pitch I/O
Type	Internal
UPC	889056189347

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Data Rate	16.0 Gbps

Grounding to Panel	No
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	42
Circuits (maximum)	42
Color - Resin	Black
Durability (mating cycles max)	250
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.942/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762μm
Plating min - Termination	2.540μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Surface Mount

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Obsolete