


PCI-7032

**Intel® Atom™ J1900/N2930 PCI Half-size SBC
with DDR3L 1333/Dual Independent Display/
Dual GbE/SATA/USB/ m-SATA/ COM/LPT**



Features

- Ultra low power, fanless Intel® Atom™ processor J1900/N2930
- Dual channel DDR3L 1066/1333 on 204-pin SO-DIMM socket
- Dual independent display
- Up to 2 GbE LAN
- Up to 1 USB 3.0 (5Gbps) and 6 USB 2.0 (480 Mbps)
- 2 SATA 2.0 (300 MB/s), one of them can be configured as m-SATA
- Legacy I/O: 4 RS-232/422/485, and 1 LPT support
- Optional module: 4 RS-232, or 4-RS-422/485, or TPM from LPC connector


Software APIs:



Specifications

Processor System	CPU	Intel Atom N2930	Intel Atom J1900
	Speed	1.83 GHz	2.0 GHz
	L2 Cache	2 MB	2 MB
	BIOS	AMI 64Mb SPI Flash	
Bus	PCI-Express		
	PCI	Four 32 bit/33 MHz PCI Masters to Backplane	
Memory	Technology	G2: Dual channel DDR3L-1333 VG: Dual channel DDR3L-1333	
	Max. Cap.	8 GB (4GB per DIMM)	
	Socket	DDR3 204-pin SO-DIMM x2	
Graphics	Onboard	Chipset integrated Intel® HD Graphics	
	VRAM	Shared system memory. It subjects to the OS.	
	Video Interface	Dual independent display: choosing two interfaces from VGA (default), LVDS (default), and DVI	
	Video Output	VGA: Supports up to 2560 x 1600 @ 60 Hz LVDS: 48 bit (Dual channel 24 bit) LVDS up to 1920 x 1200 @ 60 Hz DVI: Supports up to 2560 x 1600 @ 60 Hz Dual independent display: choosing two interface from VGA (Default), DVI and LVDS (Default)	
Ethernet	Interface	10/100/1000 Mbps	
	Controller	LAN1: Intel I211 LAN2: Intel I211 (G2)	
	Connector	RJ-45 with LED Connector x 2	
SATA	Max. Transfer Rate	300 MB/s	
	Channel	2 (SATA2 can be configured as m-SATA)	
I/O Interface	USB 2.0	G2: one USB 3.0 (5Gbps, rear I/O), six USB 2.0 (480Mbps, pin-header x6) VG: one USB 3.0 (5Gbps, rear I/O), five USB 2.0 (480Mbps, pin-header x4, rear I/O x1)	
	Serial	Four RS-232/422/485 (Extra 4 RS-232 or 4 RS-422/485 from COM modules. P/N: PCA-COM232-00A1E or PCA-COM485-00A1E)	
	Parallel	1 (EPP/ECP)	
	PS/2	1 (for mouse and keyboard, an Y cable is included in the package)	
Watchdog Timer	Output	System reset	
	Interval	Programmable, 1-255 sec/min	
Miscellaneous	Audio Output	Intel High Definition audio interface (requires a audio extension module)	
Environment	Temperature	Operating	Non-Operating
		0 ~ 60° C (32 ~ 140° F) (operating humidity: 40° C @ 85% RH Non-Condensing)	-40 ~ 85° C and 60° C @ 95% RH Non-Condensing
Power Requirement	Test Environment	Intel Celeron J1900 (2GHz), DDR3L 1333, 4GB SO-DIMM module*2	
	Voltage	12V	5V
	Current	0.737A	0.298A
Physical	Dimensions		0.044A
		185 mm (L) x 122 mm (W) (7.3" x 4.8")	

Block Diagram



* Dual display, choose two interface from VGA (Default), DVI, and LVDS (Default)

** SATA2 connector can be configured as m-SATA.

Ordering Information

Model Name	SoC	Memory	Fanless	Dual independent display	SATA/ m-SATA	USB	RS-232/ 422/485	LPT	LAN
PCI-7032G2-00A1E	J1900	Dual channel DDR3L-1333 up to 8GB (204-pin SO-DIMM socket x2)	No	Choosing 2 interfaces from VGA/DVI/LVDS	2	1 x USB 3.0 6 x USB 2.0	4	1	2
PCI-7032VG-00A1E	N2930	Dual channel DDR3L-1333 up to 8GB (204-pin SO-DIMM socket x2)	Yes	Choosing 2 interfaces from VGA/DVI/LVDS	2	1 x USB 3.0 5 x USB 2.0	4	1	1

Optional Accessories

Part Number	Description
PCA-COM485-00A1E	4x RS-422/485 module
PCA-COM232-00A1E	4 x RS-232 module
PCA-TPM-00A1E	TPM module (Trusted platform management)
1700021831-01	DVI cable
1700000265	12 pin-12 pin ATX power cable kit
1703100261	2-port USB cable kit

Packing List

Part Number	Description	Quantity
1960046526N001	CPU cooler for Atom™ J1900 SoC (only available for G2 SKU)	x 1
1700003194	Serial ATA HDD data cable	x 1
1700022749-11	Serial ATA HDD power cable	x 1
1700002223	Printer (parallel) port cable kit	x 1
1700008762	Dual COM ports cable kit	x 2
1700002343	ATX feature cable	x 1
1700014398-11	4-port USB cable kit	x 1
1700060202	Y cable for PS/2 keyboard and PS/2 mouse	x 1
9689000068	Jumper pack	x 1
2001703200	PCI-7032 startup manual	x 1
2061703200	CD with driver utility and manual (in PDF format)	x 1

Bracket View



PCI-7032G2-00A1E



PCI-7032VG-00A1E