




**Part Number :** [918143126](#)  
**Product Description :** 2.54mm Pitch C-Grid III  
Dual Row Right-Angle Shrouded Header, 26  
Circuits, Tin (Sn) over Nickel (Ni)  
**Series Number :** 91814  
**Status :** Active  
**Product Category :** PCB Headers and  
Receptacles



Documents & Resources


**Drawings**  
[918143126\\_sd.pdf](#)  
[PK-91814-005-001.pdf](#)

**3D Models and Design Files**  
[918143126\\_stp.zip](#)

**Specifications**  
[PS-99020-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

Multiple Part Industry Compliance Documents  
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	PCB Headers and Receptacles
Series	91814
Description	2.54mm Pitch C-Grid III Dual Row Right-Angle Shrouded Header, 26 Circuits, Tin (Sn) over Nickel (Ni)
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	C-Grid III
UPC	822350913744

#### Agency

UL	E29179
----	--------

#### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	350V AC/DC

#### Physical

Breakaway	No
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No

Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.432/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	2.10mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	3.048µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Through Hole

## Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
-------------	-------------

C-Grid III Female Crimp Terminals	<u>90119</u>
C-Grid III Dual Row Crimp Housings	<u>90142</u>

---

This document was generated on Mar 18, 2025