



Part Number : [2121940006](#)
Product Description : Centrality 6.00mm Top-entry,
Surface Mount Socket Assembly, Tape and Reel
Series Number : 212194
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[2121940006_sd.pdf](#)
[2121940006-PK-000.pdf](#)

3D Models and Design Files


[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2043130006-AS-000.pdf](#)
[2043130006-PS-000.pdf](#)
[2043130006-TS-000.pdf](#)
[2043131234-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	212194
Description	Sentrality 6.00mm Top-entry, Surface Mount Socket Assembly, Tape and Reel
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Name	Sentrality
UPC	191130978717

Electrical

Current - Maximum per Contact	140.0A
Voltage - Maximum	600V

Physical

Breakaway	No
-----------	----

Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	6.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	4.60mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	5.637/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Pins	<u>203263</u>

This document was generated on Sep 25, 2025