

Technical data sheet

Article number:
170-10400

HEGP04



Product Group	Standard polyester braided sleeving
Product Family	Helagaine HEGP
Material	Polyester (PET)
Colour	Black (BK)
Application Method	To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0, see page
Bundle Ø max.	7 mm
Bundle Ø min.	2 mm
Melting Point	+250 °C
Operating Temperature	-50 °C to +150 °C
Package Content packed in	metre
Pack Cont.	200 m
Specifications	ECE R-118-03 Abschnitt 6 / Annex 6, ECE R-118-03 Abschnitt 8 / Annex 8, EN 45545-2

HF ✓ RoHS ✓

EN 45545-2 **ECE R-118**