



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Single Wire Seal (SWS)**
Cavity Diameter: **15 mm [.591 in]**
Operating Temperature Range: **-40 – 130 °C [-40 – 266 °F]**
Primary Product Color: **Violet**
Primary Product Material: **Silicone**

Features

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)
----------------------------	------------------------

Body Features

Primary Product Color	Violet
Primary Product Material	Silicone

Dimensions

Wire Size	9 AWG
Cavity Diameter	15 mm[.591 in]
Compatible Insulation Diameter Range	4.6 – 5 mm[.18 – .19 in]

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
Operating Temperature (Max)	130 °C[266 °F]

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50



Contains Lubricant	Yes
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 962933-1
MPT REC 9.5 Contact SRC Sn (LP)



TE Part # 1718878-1
JPT/ AMP MCP 6.3/9.5 HSG 5 POS



TE Part # CAT-NB0-AT95
9.5 mm Automation Ready Terminals for Automotive Wire Harness Production and Advanced Assembly Automation



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 1718878-2
5POS. HSG. JPT/AMP MCP, ASS'Y, SEALED

TE Part # 2282162-1
2POS,TAB 9.5X1.2,HEADER ASSY

TE Part # 963772-2
TAB 9.5x1.2 CONTACT CF SWS Sn

TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB

TE Part # CAT-AM705-CH8172
AMP MCP, SEALED CONNECTOR HOUSING

TE Part # 1394026-1
FLA-STE-GEH9,5MM 2P

Also in the Series | AMP MCP Connector System

Automotive Connector Caps & Covers (28)

Automotive Housings(11)

Automotive Signal & Power Headers(5)

Automotive Terminals(10)

Other Automotive Connector Accessories(4)

Also in the Series | AMP MCP 9.5



Automotive Housings(11)



Automotive Seals & Cavity Plugs(3)



Automotive Signal & Power Connector Housings(3)



Automotive Terminals(10)




Connector Seals & Cavity Plugs(3)


Customers Also Bought



TE Part #HD36-24-31PT-059
PLG, 1P, LT, CBL CLMP BT, DRAIN,16, P,MC



TE Part #2-31808-2
TERMINAL, SOLIS R 8 5/16



TE Part #345807-1
ECONO CONT. TAB



TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part #1-967590-2
AMP MCP 9.5, CONTACT, SWS



TE Part #968137-6
MPQ2,8 Ag tab LL unseal. >1,0-2,5



TE Part #1394511-1
EINZELLEITDICHTG,WS



TE Part #1-1719386-1
AMP MCP 9.5, CONTACT



TE Part #2141576-1
32POS NANO MQS TL PLUG HOUSING, CODE A

Documents



Product Drawings

MCP9,5 EINZELDICHTG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1355437-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1355437-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1355437-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German