



Part Number : [11030043](#)
Product Description : Extraction Tool for Micro-Fit
Terminals
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand
Tools
Engineering Number : HT60923A



Documents & Resources

Tooling Specifications

- [ATS-011030043-001.pdf](#)
- [TM-638000029-001.pdf](#)
- [TM-638000029DE-001.pdf](#)
- [TM-638000029SP-001.pdf](#)
- [TM-638000029FR-001.pdf](#)
- [TM-638000029IT-001.pdf](#)
- [TM-638000029JP-001.pdf](#)
- [TM-638000029KR-001.pdf](#)
- [TM-638000029MY-001.pdf](#)
- [TM-638000029PL-001.pdf](#)
- [TM-638000029RU-001.pdf](#)
- [TM-638000029SK-001.pdf](#)
- [TM-638000029TH-001.pdf](#)
- [TM-638000029VN-001.pdf](#)
- [TM-638000029CN-001.pdf](#)
- [TM-638000029TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Extraction Tool for Micro-Fit Terminals
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800754211260

Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
---------------------	--

Physical

Net Weight	3.975/zg
------------	----------

Applicable Parts

Description	Part Number
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430300001</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430300002</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430300003</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430300004</u>

Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430300005</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430300006</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Bag	<u>430300007</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Bag	<u>430300008</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Bag	<u>430300009</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 30-26 AWG, Bag	<u>430300010</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Bag	<u>430300011</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Bag	<u>430300012</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430300038</u>
Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430300039</u>

Micro-Fit 3.0 Crimp Terminal, Female, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430300040</u>
Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430310001</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430310002</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430310003</u>
Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430310004</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430310005</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430310006</u>
Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Bag	<u>430310007</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Bag	<u>430310008</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Bag	<u>430310009</u>
Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 30-26 AWG, Bag	<u>430310010</u>

Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Bag	<u>430310011</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Bag	<u>430310012</u>
Micro-Fit 3.0 Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430310021</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430310022</u>
Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	<u>430310023</u>
Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315003</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315004</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315005</u>
Micro-Fit TPA Crimp Terminal, Male, with 2.54µm Matte Tin Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315006</u>
Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430315007</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated	<u>430315008</u>

Phosphor Bronze Contact, 30-26 AWG, Reel	
Micro-Fit TPA Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430315009</u>
Micro-Fit TPA Crimp Terminal, Male, with 2.54µm Matte Tin Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>430315010</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>457730001</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>457730003</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Gold (Au) Plated Phosphor Bronze Contact, 30-26 AWG, Reel	<u>457730006</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>457730053</u>
Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 24-20 AWG, without Lubricant	<u>462350001</u>
Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.76µm Selective Gold (Au) over Nickel (Ni), 24-20 AWG, without Lubricant	<u>462350002</u>
Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 30-26 AWG, without Lubricant	<u>462350003</u>
Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female,	<u>462350004</u>

with .076µm Selective Gold (Au) over Nickel (Ni), 30-26 AWG, without Lubricant	
Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 24-20 AWG, with Lubricant	<u>462355001</u>
Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.76µm Selective Gold (Au) over Nickel (Ni), 24-20 AWG, with Lubricant	<u>462355002</u>
Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 30-26 AWG, with Lubricant	<u>462355003</u>
Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with .076µm Selective Gold (Au) over Nickel (Ni), 30-26 AWG, with Lubricant	<u>462355004</u>
2.00mm Pitch MicroBlade Wire-to-Wire Crimp Terminal, Female, 30-24 AWG, Reel	<u>500118000</u>
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 32-28 AWG, Reel	<u>500588000</u>
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 32-28 AWG, Reel	<u>500588001</u>
1.25mm Pitch, PicoBlade Female Crimp Terminal, Gold (Au) Plating, 32-28 AWG, Reel	<u>500588020</u>
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 32-28 AWG, Bag	<u>500588100</u>
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Reel	<u>500798000</u>
1.25mm Pitch, PicoBlade Female	<u>500798001</u>

Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Reel	
1.25mm Pitch, PicoBlade Female Crimp Terminal, Gold (Au) Flash Plating, 28-26 AWG, Reel	<u>500798020</u>
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Bag	<u>500798100</u>
1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Reel	<u>501258000</u>
1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 28-26 AWG, Bag	<u>501258100</u>
1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 32-28 AWG, Reel	<u>501338000</u>
1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 32-28 AWG, Bag	<u>501338100</u>
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 30-24 AWG, Reel	<u>502128000</u>
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 30-24 AWG, Bag	<u>502128100</u>
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Reel	<u>503728000</u>
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Bag	<u>503728100</u>
OBD-II Crimp Terminal, Female, 50420, 4.00mm Pitch	<u>504208000</u>
Micro-Fit High-Current RMF Crimp Terminal, Female, 2.540µm Bright Tin Plating, 18 AWG	<u>2039510001</u>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 30-26 AWG	<u>2064600011</u>
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 30-26	<u>2064600012</u>

AWG	
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 30-26 AWG	<u>2064600013</u>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 24-20 AWG	<u>2064600021</u>
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 24-20 AWG	<u>2064600022</u>
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 24-20 AWG	<u>2064600023</u>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 18 AWG	<u>2064600031</u>
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 18 AWG	<u>2064600032</u>
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 18 AWG	<u>2064600033</u>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 16 AWG	<u>2064600041</u>
Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 16 AWG	<u>2064600042</u>
Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 16 AWG	<u>2064600043</u>
OneBlade Crimp Terminal, Female, Tin (Sn) Plating, 30-28 AWG, Reel	<u>2140935000</u>
OneBlade Crimp Terminal, Female, Tin (Sn) Plating, 32-30 AWG, Reel	<u>2140935100</u>
DuraClik Crimp Terminal, Female, 26-22 AWG, Tin (Sn) Plating, Reel	<u>5600850101</u>

This document was generated on Sep 22, 2025