

DIN-Signal high curr. f, 40A crimp AU50



Part number	09 03 000 8215
Specification	DIN-Signal high curr. f, 40A crimp AU50
HARTING eCatalogue	https://harting.com/09030008215

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Series	DIN 41612
Type of contact	Crimp contact
Description of the contact	Straight
Contacts for	DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5 DIN 41612 Bauform M 0+2

Version

Termination method	Crimp termination
Gender	Female contact for female connectors
Connection type	Motherboard to daughtercard Mezzanine Extender card PCB to cable
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	10 mm ²
Conductor cross-section [AWG]	AWG 8
Rated current	≤40 A
Insertion force	≤10 N
Withdrawal force	≥1.6 N

Technical characteristics

Performance level	AU 50
	1
	acc. to IEC 60603-2
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side Noble metal Termination side
Layer thickness	≥1.27 µm
Layer thickness	≥50 µinch
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	DIN 41626
----------------	-----------

Commercial data

Packaging size	100
Net weight	2.16 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140215320
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796

Commercial data

UNSPSC 24.0

39121522

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2

