



Part Number : [11030016](#)


Product Description : Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals

Series Number : 207121

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools

Engineering Number : HTA2174



Documents & Resources

Tooling Specifications

[ATS-011030016-001.pdf](#)

[TM-638000029-001.pdf](#)

[TM-638000029DE-001.pdf](#)

[TM-638000029SP-001.pdf](#)

[TM-638000029FR-001.pdf](#)

[TM-638000029IT-001.pdf](#)

[TM-638000029JP-001.pdf](#)

[TM-638000029KR-001.pdf](#)

[TM-638000029MY-001.pdf](#)

[TM-638000029PL-001.pdf](#)

[TM-638000029RU-001.pdf](#)

[TM-638000029SK-001.pdf](#)

[TM-638000029TH-001.pdf](#)

[TM-638000029VN-001.pdf](#)

[TM-638000029CN-001.pdf](#)

[TM-638000029TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
------------	--------------

China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals
Comments	See Tooling Specification (PDF) Above
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Flat Blade,KK,KK 396,MarKK,Mini-

	Lock,Trifurcon,Ultra-Fit
Tool Type	Extraction Hand Tool
UPC	800753619951
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Flat Blade Crimp Terminal, Series 1508, Female, With Tin (Sn) Plated Brass Contact, Single 20-14 AWG or Double 18+18 or 20+20 AWG, Reel	<u>05060117</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass Tin (Sn)	<u>08500105</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass Tin (Sn)	<u>08500106</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 2.540µm Tin (Sn)	<u>08500107</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 2.540µm Tin (Sn)	<u>08500108</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 2.54µm Tin (Sn)	<u>08500111</u>
KK 396 Crimp Terminal 2478, 24-18	<u>08500119</u>

AWG, Reel, Brass, 3.8µm Tin (Sn)	
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 3.8µm Tin (Sn)	<u>08500120</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 2.540µm Tin (Sn)	<u>08500133</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 2.540µm Tin(Sn)	<u>08500134</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Brass Tin (Sn)	<u>08500183</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Brass Tin (Sn)	<u>08500185</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Reel, Brass Tin (Sn)	<u>08500187</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Bag, Brass Tin (Sn)	<u>08500189</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 3.87µm Tin (Sn)	<u>08500281</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, Tin (Sn)	<u>08520071</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, Tin (Sn)	<u>08520072</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Reel, Phosphor Bronze Tin(Sn)	<u>08520112</u>
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Bag, Phosphor Bronze Tin (Sn)	<u>08520113</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Tin(Sn)	<u>08520124</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Tin (Sn)	<u>08520125</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 5.0µm Tin (Sn)	<u>08520811</u>

KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 5.0µm Tin (Sn)	<u>08520812</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.38µm Selective Gold (Au)	<u>08550103</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 0.38µm Selective Gold (Au)	<u>08550104</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.38µm Selective Gold (Au)	<u>08550105</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 0.38µm Selective Gold(Au)	<u>08550106</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.76µm Select Gold (Au) over Gold Flash	<u>08550123</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.76µm Gold (Au)	<u>08550133</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 0.76µm Gold (Au)	<u>08550134</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Left Payoff Reel, Brass, 0.76µm Select Gold (Au) over Gold Flash	<u>08550137</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.51µm Selective Gold (Au)	<u>08560105</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Brass, 0.51µm Selective Gold (Au)	<u>08560106</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.38µm Select Gold (Au) over Gold Flash	<u>08560107</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 0.38µm Select Gold (Au) over Gold Flash	<u>08560108</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Gold (Au)	<u>08560123</u>

KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Gold(Au)	<u>08560124</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Selective Gold (Au)	<u>08580110</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Bag, Phosphor Bronze Selective Gold (Au)	<u>08580111</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.76µm Gold (Au)	<u>08580114</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 0.76µm Gold (Au)	<u>08580115</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au)	<u>08580121</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 0.51µm Selective Gold (Au)	<u>08580122</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au) over Gold Flash	<u>08580125</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au) over Gold Flash	<u>08580126</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Gold (Au)	<u>08580187</u>
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Bag, Phosphor Bronze Gold(Au)	<u>08580189</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 3.810µm Tin (Sn)	<u>08600003</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 3.810µm Tin (Sn)	<u>08600004</u>
KK 396 Crimp Terminal 2578, 26-22	

AWG, Reel, Phosphor Bronze, 0.76µm Select Gold (Au) over Gold Flash	<u>08650110</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>08650114</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>08650115</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>08650116</u>
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>08650117</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Selective Gold (Au)	<u>08650121</u>
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Selective Gold (Au)	<u>08650122</u>
KK 396 Crimp Terminal 2478, 24-18 AWG, Reel, Brass, 0.9µm Pre-Plated Tin (Sn)	<u>39000286</u>
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Pre- Tinned Plating, Reel	<u>455703000</u>
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Tin (Sn) over Nickel (Ni) Plating, Reel	<u>455703002</u>
3.96mm (.156") Pitch MarKK Crimp Terminal, 20-18 AWG, Tin (Sn) over Nickel (Ni) With Select Gold (Au) Plating, Reel	<u>455703004</u>
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Pre- Tinned Plating, Bag	<u>455703050</u>
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Tin (Sn) over Nickel (Ni) Plating, Bag	<u>455703052</u>
3.96mm (.156") Pitch MarKK Crimp Terminal, 20-18 AWG, Tin (Sn) over	<u>455703054</u>

Nickel (Ni) With Select Gold (Au) Plating, Bag	
Icemaker Crimp Terminal Humpback with Anti-Fish Hook	<u>456060004</u>
2.00mm Pitch Crimp Terminal, Male, Phosphor Bronze, 0.76µm Gold (Au) Plating, Reel	<u>506398028</u>
2.00mm Pitch Crimp Terminal, Male, Phosphor Bronze, 0.76µm Gold (Au) Plating, Bag	<u>506398128</u>
2.50mm Pitch, Mini-Lock Male Crimp Terminal, Tin Plating, 28-22 AWG, Reel	<u>508378000</u>
2.50mm Pitch, Mini-Lock Male Crimp Terminal, Tin Plating, 28-22 AWG, Bag	<u>508378100</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 16+16 or Single 12 AWG, Reel	<u>768230343</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	<u>768230344</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, 10 AWG, Reel	<u>768230345</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	<u>1720630333</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	<u>1720630334</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 10 AWG, Reel	<u>1720630335</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	<u>1720631333</u>

Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	<u>1720631334</u>
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 10 AWG, Reel	<u>1720631335</u>
3.96mm Pitch EdgeMate Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 20-18 AWG, Reel	<u>1721601803</u>
3.96mm Pitch EdgeMate Crimp Terminal, Brass, Gold (Au), Bifurcated, 20-18 AWG, Reel	<u>1721601805</u>

This document was generated on Sep 17, 2025