

PRODUCT DESCRIPTION CODE :

10142532-0XX LF



—RoHS COMPATIBLE

—FOR CUSTOMER CODE:
BLANK = GENERAL USE

—PACKAGING :
BLANK = BULK



—NUMBER OF POSITIONS : 02 TO 03

—MATERIAL



NOTES:


- 1 - MATERIAL:
HIGH TEMPERATURE THERMOPLASTIC
COLOR BLACK UL94 V-0
- 2 - PACKAGING : BULK
- 3 - FOR USE WITH MINITEK μ SPACE CTW TERMINALS :
AWG 26-30, SERIE 10141272 & 10148496
- 4 - TO BE MATED WITH MINITEK μ SPACE HEADERS SERIES
10142534 / 10143714
- 5 - RoHS COMPLIANT, THE PRODUCT IS NOT INTENDED TO BE
EXPOSED TO ANY SOLDER PROCESS.
- 6 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHERS
COUNTRY REGULATIONS AS PER GS-022-008




PRE-LOAD CONFIGURATION : DELIVERED STATUS

spec ref		GS-12-1422		dr	Sawanth, Ambaa	2017/07/06	projection	mm	size	A3	scale	5:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Cyril Jeune	2019/04/23			ecn no		ELX-F-27419-1		
				chr	Hyppias, Arnau	2019/04/23			rel level				Released
				appr	Beatrice Vial	2019/04/23							
ISO 406							product family		-				
ISO 1101													
surface	linear	0.X	±0.3	Amphenol FCI	title	RECEPTACLE ASSEMBLY			dwg no	10142532		rev	B
		0.XX	±0.10										
		0.XXX	±0.005										
	ISO 1302	angular	0°										


PART NO.	NO. OF POSN	DIM "A"
10142532-002LF	02	5.35
10142532-003LF	03	6.85




PRE-LOAD CONFIGURATION FOR TERMINAL INSERTION




FINAL LOAD CONFIGURATION WITH INSERTED TERMINAL




FULL HEADER AND RECEPTACLE ASSEMBLY CONFIGURATION




POSITION NUMBER INDICATION FOR 3POS


spec ref		GS-12-1422		dr	Sawanth, Ambaa	2017/07/06	projection 	mm 	size	A3	scale	5:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Cyril Jeune	2019/04/23			ecn no		ELX-F-27419-1		
ISO 406 ISO 1101				chr	Hyppias, Arnau	2019/04/23			rel level				Released
				appr	Beatrice Vial	2019/04/23	product family		-				
surface  ISO 1302	linear	0.X	±0.3	Amphenol FCI	title	RECEPTACLE ASSEMBLY MINITEK μSPACE STS 1.5 TOP LATCH			dwg no	10142532		rev	B
		0.XX	±0.10										
		0.XXX	±0.005										
		angular	0°	±2°		cat. no.	-	Product - Customer Drw			sheet 2 of 3		



TEST PROBE $\varnothing$ 0.4mm COMPLIANCE





RECOMMENDED LAYOUT OF TEST PROBE $\varnothing$ 0.4mm



HOLE FOR TEST PROBE

DETAIL A
SCALE 20:1

spec ref		GS-12-1422			dr	Sawanth, Ambaa	2017/07/06	projection 		size	A3	scale	3:1
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Cyril Jeune	2019/04/23	ecn no			ELX-F-27419-1			
				chr	Hyppias, Arnau	2019/04/23							
				appr	Beatrice Vial	2019/04/23		product family					-
surface  ISO 1302	linear	0.X	±0.3		title RECEPTACLE ASSEMBLY				dwg no	10142532			rev B
		0.XX	±0.10										
		0.XXX	±0.005		MINITEK μSPACE STS 1.5 TOP LATCH								
	angular	0°	±2°	cat. no.					-	Product - Customer Drw			