

[Find by Feature](#)
[Browse by Category](#)
[Share](#)
 [Search →](#)

Enter part number or keyword

[Search Results \(0\)](#)
[Search Options](#)

Select a product type to narrow your search:

Terminal ▼

Results with your selections: --

Blade size [mm] ▼

Terminal family ▼

Material ▼

Plating ▼

Gender ▼

Sealed ▼

Inside Ring Diameter [mm] ▼

Outside Ring Diameter [mm] ▼

Minimum Cable Core Cross Section [mm²] ▼


Maximum Cable Core Cross Section [mm²] ▼

Minimum Cable Diameter [mm] ▼

Maximum Cable Diameter [mm] ▼

[Clear](#)
[Search →](#)

Female Printed Circuit Edge Board Standard Tin Plated Terminal, Cable Range 0.50 - 0.35 mm², Cable Insulation Range 2.20 - 1.30 mm Part #12066273



[Question about this product?](#)

[Attributes](#)
[Documents \(1\)](#)

Part #:	12066273
Description:	Female Printed Circuit Edge Board Standard Tin Plated Terminal, Cable Range 0.50 - 0.35 mm ² , Cable Insulation Range 2.20 - 1.30 mm
Product Type:	Terminal
Status:	Active
Terminal family:	Printed Circuit
Series:	EDGBD-STD
Gender:	Female
Sealed:	Unsealed
Material:	Tin Brass
Plating:	Tin Plated
Minimum Cable Core Cross Section [mm²]:	0.35
Maximum Cable Core Cross Section [mm²]:	0.50
Minimum Cable Diameter [mm]:	1.30
Maximum Cable Diameter [mm]:	2.20
Weight [g]:	1

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.