




view shown without plastic pin




PC card drilling dimensions(after plating)
(thickness 1.60 or 2.40±0.20mm)



SHELL	A±0.38	B±0.12	C±0.10	D $+0.25$	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 $+0.15$	D09P80C4PV00	D09P80C6PV00
15	39.14	33.32	26.32	25.12	19.18	5.90 $+0.15$	D15P80C4PV00	D15P80C6PV00
25	53.03	47.04	40.04	38.84	33.12	5.70 $+0.25$	D25P80C4PV00	D25P80C6PV00
37	69.32	63.50	56.50	55.30	49.68	5.70 $+0.25$	D37P80C4PV00	D37P80C6PV00
							Gold flash	0.76 → gold

Detail of plastic pin



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title		
E	ELX-I-17859	MP	2014/06/06	angles	linear				
				0°±2'					
				dr	PESSON	1995/10/27	dwg no		
				engr	MITHUN PAUL	2014/06/06			
				chr	ALIAS BABU	2014/06/06			
				appd	BIJU K PAUL	2014/06/06	sheet 1 of 1 size		
sheet index	revision	E							
	sheet	1							
							C01-8646-0407		
							A3		
							type Product Customer Drawing		

