

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	REVISED PER ECR-21-117154	03AUG2022	SKR	VS

1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.

2 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.

3 DIMENSIONS IN BRACKETS ARE IN INCHES.


4 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 - 0.00178 [.000050 - .000070] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.

5 DRAIN HOLES LOCATED AS SHOWN. OPTIONAL CONSTRUCTION- ALL DRAIN HOLES LOCATED 90° AS SHOWN IN DETAIL A.

6 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 - 0.00178 [.000050 - .000070] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND MATTE TIN ON SOLDER TAIL END.



7 SUPERSEDED BY 794783-3

8. DIMENSION SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



3-DIMENSIONAL MODEL
NTS

△	PHOSPHOR BRONZE, GOLD	6	NYLON,UL94V-0,BLACK	794783-3
	PHOSPHOR BRONZE, GOLD	4	NYLON,UL94V-0,BLACK	794783-2
	PHOSPHOR BRONZE, PRE-TIN		NYLON,UL94V-0,BLACK	794783-1
	CONTACT MATERIAL AND FINISH		HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. McEACHIN 19-JUN-2000	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK K. COBLE 19-JUN-2000				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ± 0°30' ANGLES	APVD K. COBLE 19-JUN-2000	NAME			
		PRODUCT SPEC	SOCKET HEADER ASSEMBLY, POLARIZED,4 CIRCUIT UNIVERSAL MATE-N-LOK™			
MATERIAL SEE TABLE	FINISH SEE TABLE	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT 0.000000	A1	00779	C=794783	-
CUSTOMER DRAWING		SCALE	SHEET	OF	REV	
		5:1	1	1	B3	

