OMRON Industrial Automation



E32-TC200 2M

Fiber optic sensor head, through-beam, M4 cylindrical axial, R25 fiber, 2 m cable

Downloaded from Arrow.com.

Specifications

Sensing method	Through-beam
Shape	Threaded
Size	M4
Application	Object detection
Temperature range	-40-70 °C
Sensing distance	2300 mm
Cable length	2 m
Sleeve diameter	-8888 mm
Sleeve length	-8888 mm
Bending radius	25 mm
Free cut	✔
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Top-view
Material sheath	Polyethylene

Accessories

	**E39-F1.**	Long-distance lens unit for E32 through-beam fibers with M2.6 thread
	**E39-F2**	Focal lens, side view unit for E32 through-beam optical fibers

Downloaded from Arrow.com.

Related products



E3X-ZV and E3X-MZV
Smart Fiber Amplifier



E3NX-CA
High-performance color mark sensor



E3NX-CA
High-performance color mark sensor



E3NX-MA
Smart Fiber Amplifier Units



E3X-NA
Digital fiber amplifier with potentiometer adjustment



E3NX-FA
High-performance digital fiber amplifier

Downloads

CAD Library



Fiber Optic Sensors
Group Catalogue

EN PDF 7.54 MB

Downloaded from Arrow.com.

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 6 August, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.