




Technical drawing of a mechanical part with dimensions and a coordinate system. The part is symmetrical about a vertical dashed centerline. Dimensions include a total width of 7.15, a left-side width of 0.35, a central width of 0.65, and a right-side width of 0.28. Vertical dimensions on the left are 1.00, 0.78, and 0.65. Vertical dimensions on the right are 1.00 and 1.35. A horizontal distance of 2.60 is marked from the centerline to the right edge of the central section. Five points are marked: 1 (top left), 2 (bottom left), 3 (top center), 4 (bottom center), and 5 (top right). A hole is specified as $\varnothing 0.40$ and a fillet as $R0.175$.

Technical drawing of a mechanical part, likely a shaft or pin, showing dimensions in millimeters. The dimensions are:


- 2.35
- 1.91
- 1.00
- 0.74
- 0.80
- 0.15
- 2.9



H
G
F
E
D
C
B
A



Products P/N	PCS/Reel	Reels/Carton	PCS/Carton
USB3131	1,500	10	15,000



Part Number USB3131		Product Description Micro USB Receptacle, Type B, Through-Hole, Vertical, With 2.30mm (Standard) Shell Stakes			This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	 www.gct.co
Drawing Date 28th October 2013						
By CC	Detail USB3131 B PCN	Tolerances (Except as Noted) Length	Angle			
Revision BS	Date 07/10/20					