

SFGH WM4 C BT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**WM4 C photovoltaic connectors**

- one crimp contact for 4 mm² and 6 mm² cables
- TÜV approval according to the latest standard DIN EN 50521
- Can be loaded with a rated current of up to 35 A

General ordering data

Type	SFGH WM4 C BT
Order No.	1530700000
Version	Photovoltaics, Plug-in connector, Pin
GTIN (EAN)	4050118335330
Qty.	100 pc(s).

SFGH WM4 C BT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	13.8 g
------------	--------

Technical data

Approvals	TÜV (DIN EN 50521)	Cable type	2 Pfg1169/08.07, EN 50618:2014
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	4 mm ²
External thread	M 16	Outer cable diameter, max.	7 mm
Outer cable diameter, min.	5.5 mm	Pollution severity	2
Protection degree	IP65, IP67, IP2x open	Rated current	35 A
Rated voltage	1500 V DC (IEC)		

Classifications

ETIM 5.0	EC000379	ETIM 6.0	EC002928
eClass 6.2	22-57-02-90	eClass 7.1	27-44-05-01
eClass 8.1	27-44-05-01	eClass 9.0	22-57-92-03
eClass 9.1	27-44-01-07		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	BPZL WM4C LANG