

RED INDICATES ORIGINAL

DWG SIZE B			DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.			REVISIONS		315-0056		SH 1	
						REV A	ED	DESCRIPTION PRODUCTION RELEASE	DWN DKC	APPROVED	DATE

DASH NO	CABLES ACCOMMODATED	ASSEMBLE PER
-201	M17/176-00002	TAI-143

INCH	MM
.005	0.13
.030	0.76
.255	6.48
.334	8.48
.455	11.56
1.146	29.11

4. SAME AS PL3155AC-201 EXCEPT MATING INTERFACE GASKET AND SHRINK SLEEVING NOT SUPPLIED. CONNECTOR SHALL MEET OUTGASSING REQUIREMENTS.

QUANTITY: 20

CONNECTORS SHALL BE FROM THE SAME LOT/DATE CODE.
 100% INSULATION RESISTANCE TEST: 5,000 MEGOHMS
 MINIMUM AT 500 VDC.

3. THREADED SUBMINIATURE CONCENTRIC TWINAX/TRIAX FULL CRIMP CABLE PLUG

2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES

.255 HEX

RECOMMENDED
HEX CRIMP
SCALE: NONE

QTY	DESCRIPTION	PART NUMBER	ITEM
TROMPETER ELECTRONICS, INC.		PL3155AC/PL3155ACS	
TOL UNLESS SPECIFIED .XX ±.03 .XXX ±.005 .XXXX± ANGLES±			
DWN	DKC 2-24-97	MATERIAL	CODE IDENT
CHK	BW 3-4-97		14949
ENGR			
APPR	Fa 3/2/97	SCALE 4/1	DATE 3/18/97

NEXT ASSY		DATE 3/18/97	SHEET 1 OF 2
-----------	--	--------------	--------------