
Part Number : 2083934003
Product Description : 1.00mm Pitch, Pico-Clasp Low-Halogen PCB Header, Dual Row, Right-Angle, Surface Mount, 0.76µm Gold Plated, Inner Positive Lock, 40 Circuits, Natural
Series Number : 208393
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2083934003_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

2083934003.dxf

Specifications

5011890000-AS-001.pdf

2083939200-SPK-200.pdf

5011890000-PS-002.pdf

5011891000-PS-002.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:a8b6af20-

Downloaded from Arrow.com.

	e731-45d8-9f93-e8688a3aac82
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	208393
Description	1.00mm Pitch, Pico-Clasp Low-Halogen PCB Header, Dual Row, Right-Angle, Surface Mount, 0.76µm Gold Plated, Inner Positive Lock, 40 Circuits, Natural
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	Pico-Clasp
UPC	193264194353

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	40
Circuits (maximum)	40
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	1084.000/mg
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.760µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number

Downloaded from Arrow.com.

Pico-Clasp Low-Halogen Dual Row Receptacle Housings	501189

This document was generated on Dec 16, 2025

Downloaded from Arrow.com.