

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


KEYING




KEY CODE "A"




KEY CODE "B"




KEY CODE "C"




KEY CODE "D"





KEY CODE "E"





KEY CODE "F"



















PLUG HOUSING IN FINAL LOCKED POSITION (TPA ENGAGED)



UNMATE PLUG FROM HEADER WITH SCREWDRIVER RECOMMENDED SIZE: 50 X 2.5MM

PUSH DOWN IN SPACING BETWEEN PLUG LATCH WINDOW AND HEADER TO DEPRESS LATCH THEN ROTATE SCREWDRIVER TOWARDS HEADER TO REMOVE PLUG FROM HEADER ASSEMBLY



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECO-16-000849	21JAN2016	DD	MB
	A3	REVISED PER ECO-16-001287	28JAN2016	DD	MB

1. COMPANY LOGO AND PART NUMBER
2. MATERIAL IDENTIFIER
3. DATE WHEEL
4. MOLD CAVITY ID

5. MAX WIRE SIZE RANGE 0.75mm^2 FLR. SEE CABLE HARNESS DRAWINGS FOR NUMBER OF CABLES CURRENT CARRYING CAPACITY FOR CONTACT LOCATED IN MICRO QUADLOCK SYSTEM PRODUCT SPECIFICATION: 108-18030

6. OPTIONAL VOID CORING
7. OPTIONAL DATE WHEEL LOCATION
8. OPTIONAL MATERIAL IDENTIFIER LOCATION
9. OPTIONAL MOLD CAVITY ID LOCATION

COLOR	KEY	MATERIAL	DESCRIPTION	TE PART NUMBER
GREEN	E	PBT-GF15	2 POSN MQS PLUG	5-2138650-1
VIOLET	D	PBT-GF15		4-2138650-1
NATURAL	B	PBT-GF15		2-2138650-1
BLACK	A	PBT-GF15		1-2138650-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±0.1
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL - 2

FINISH - -

DWN PAUL ROMAN 11OCT2011
CHK PAUL ROMAN 11OCT2011
APVD PAUL ROMAN 11OCT2011
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME PLUG HOUSING, 2 POSITION MQS UNSEALED (1-PIECE) -

SIZE A1 | CAGE CODE 00779 | DRAWING NO C-2138650 | RESTRICTED TO -

CUSTOMER DRAWING | SCALE 7:1 | SHEET 1 OF 1 | REV A3

4805 (3/13)

Downloaded from Arrow.com.