

D-MBKKB 2,5 - End cover

1413052

<https://www.phoenixcontact.com/ae/products/1413052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 40 mm, width: 5 mm, height: 62 mm, color: gray



Commercial data

Item number	1413052
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE1
Product key	BE1Z1X
GTIN	4017918021139
Weight per piece (including packing)	2.86 g
Weight per piece (excluding packing)	2.7 g
Customs tariff number	85389099
Country of origin	DE

D-MBKKB 2,5 - End cover



1413052

<https://www.phoenixcontact.com/ae/products/1413052>

Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2
Static insulating material application in cold	-40 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Dimensions

Width	5 mm
Height	62 mm
Depth	40 mm
Depth on NS 35/7,5	47.5 mm

D-MBKKB 2,5 - End cover

1413052

<https://www.phoenixcontact.com/ae/products/1413052>



Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-MBKKB 2,5 - End cover

1413052

<https://www.phoenixcontact.com/ae/products/1413052>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com