

# MOSFET - Power, Single N-Channel, SO8FL

**40 V, 2.35 mΩ, 111 A**

**NTMFS2D3N04XM**

## Features

- Low  $R_{DS(on)}$  to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Small Footprint (5 x 6 mm) with Compact Design
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

## Applications



- Motor Drive
- Battery Protection
- Oring

## MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise stated)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	$V_{DSS}$	40	V
Gate-to-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current	$I_D$	111	A
		78	
Power Dissipation	$P_D$	53	W
Continuous Drain Current $R_{\theta JA}$	$I_{DA}$	29	A
		21	
Pulsed Drain Current	$I_{DM}$	682	A
Operating Junction and Storage Temperature Range	$T_J, T_{STG}$	-55 to +175	°C
Source Current (Body Diode)	$I_S$	76	A
Single Pulse Avalanche Energy ( $I_{PK} = 6.5$ A)	$E_{AS}$	155	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)	$T_L$	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

$V_{(BR)DSS}$	$R_{DS(on)}$ MAX	$I_D$ MAX
40 V	2.35 mΩ @ $V_{GS} = 10$ V	111 A



**DFN5 (SO8-FL)  
CASE 488AA**



2D3N4 = Specific Device Code  
A = Assembly Location  
Y = Year  
W = Work Week  
ZZ = Assembly Lot Code

## ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

## THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Note 2)	$R_{\theta JC}$	2.82	$^{\circ}\text{C}/\text{W}$
Thermal Resistance, Junction-to-Ambient (Notes 1, 2)	$R_{\theta JA}$	41.1	

1. Surface mounted on FR4 board using 650 mm<sup>2</sup>, 2 oz Cu pad.

2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

ELECTRICAL CHARACTERISTICS ( $T_J = 25^{\circ}\text{C}$  unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
-----------	--------	----------------	-----	-----	-----	------

## OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0 \text{ V}, I_D = 1 \text{ mA}, T_J = 25^{\circ}\text{C}$	40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(\text{BR})\text{DSS}}/\Delta T_J$	$I_D = 1 \text{ mA}, \text{Referenced to } 25^{\circ}\text{C}$		15		$\text{mV}/^{\circ}\text{C}$
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{\text{DS}} = 40 \text{ V}, T_J = 25^{\circ}\text{C}$			10	$\mu\text{A}$
		$V_{\text{DS}} = 40 \text{ V}, T_J = 125^{\circ}\text{C}$			100	
Gate-to-Source Leakage Current	$I_{\text{GSS}}$	$V_{\text{GS}} = 20 \text{ V}, V_{\text{DS}} = 0 \text{ V}$			100	nA

## ON CHARACTERISTICS

Drain-to-Source On Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = 10 \text{ V}, I_D = 20 \text{ A}, T_J = 25^{\circ}\text{C}$		2.03	2.35	$\text{m}\Omega$
Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{GS}} = V_{\text{DS}}, I_D = 60 \mu\text{A}, T_J = 25^{\circ}\text{C}$	2.5		3.5	V
Gate Threshold Voltage Temperature Coefficient	$\Delta V_{\text{GS}(\text{TH})}/\Delta T_J$	$V_{\text{GS}} = V_{\text{DS}}, I_D = 60 \mu\text{A}$		-7.21		$\text{mV}/^{\circ}\text{C}$
Forward Trans-conductance	$g_{\text{FS}}$	$V_{\text{DS}} = 5 \text{ V}, I_D = 20 \text{ A}$		89.2		S

## CHARGES, CAPACITANCES &amp; GATE RESISTANCE

Input Capacitance	$C_{\text{ISS}}$	$V_{\text{GS}} = 0 \text{ V}, V_{\text{DS}} = 20 \text{ V}, f = 1 \text{ MHz}$		1421		pF
Output Capacitance	$C_{\text{OSS}}$			1015		
Reverse Transfer Capacitance	$C_{\text{RSS}}$			24		
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$	$V_{\text{GS}} = 10 \text{ V}, V_{\text{DD}} = 20 \text{ V}, I_D = 50 \text{ A}$		22.1		nC
Threshold Gate Charge	$Q_{\text{G}(\text{TH})}$			4.18		
Gate-to-Source Charge	$Q_{\text{GS}}$			6.68		
Gate-to-Drain Charge	$Q_{\text{GD}}$			4.07		
Gate Resistance	$R_G$	$f = 1 \text{ MHz}$		0.93		$\Omega$

## SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{\text{d}(\text{ON})}$	Resistive Load, $V_{\text{GS}} = 0/10 \text{ V}, V_{\text{DD}} = 20 \text{ V},$ $I_D = 50 \text{ A}, R_G = 0 \Omega$		15.8		ns
Rise Time	$t_r$			5.19		
Turn-Off Delay Time	$t_{\text{d}(\text{OFF})}$			22.2		
Fall Time	$t_f$			4.69		

## SOURCE-TO-DRAIN DIODE CHARACTERISTICS

Forward Diode Voltage	$V_{\text{SD}}$	$V_{\text{GS}} = 0 \text{ V}, I_S = 20 \text{ A}, T_J = 25^{\circ}\text{C}$		0.82		V
		$V_{\text{GS}} = 0 \text{ V}, I_S = 20 \text{ A}, T_J = 125^{\circ}\text{C}$		0.69		
Reverse Recovery Time	$t_{\text{RR}}$	$V_{\text{GS}} = 0 \text{ V}, I_S = 50 \text{ A},$ $dI/dt = 100 \text{ A}/\mu\text{s}, V_{\text{DD}} = 20 \text{ V}$		33.3		ns
Charge Time	$t_a$			14.6		
Discharge Time	$t_b$			18.7		
Reverse Recovery Charge	$Q_{\text{RR}}$			23.1		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs.  $V_{GS}$




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature










Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS



# NTMFS2D3N04XM

## TYPICAL CHARACTERISTICS




Figure 13. Transient Thermal Response

## ORDERING INFORMATION

Device	Marking	Package	Shipping <sup>†</sup>
NTMFS2D3N04XMT1G	2D3N4	DFN5 (Pb-Free)	1500 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


## PACKAGE DIMENSIONS

## DFN5 5x6, 1.27P

(SO-8FL)

CASE 488AA

ISSUE N




STYLE 1:  
 PIN 1. SOURCE  
 2. SOURCE  
 3. SOURCE  
 4. GATE  
 5. DRAIN

STYLE 2:  
 PIN 1. ANODE  
 2. ANODE  
 3. ANODE  
 4. NO CONNECT  
 5. CATHODE

NOTES:  
 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.  
 2. CONTROLLING DIMENSION: MILLIMETER.  
 3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.00	---	0.05
b	0.33	0.41	0.51
c	0.23	0.28	0.33
D	5.00	5.15	5.30
D1	4.70	4.90	5.10
D2	3.80	4.00	4.20
E	6.00	6.15	6.30
E1	5.70	5.90	6.10
E2	3.45	3.65	3.85
e	1.27 BSC		
G	0.51	0.575	0.71
K	1.20	1.35	1.50
L	0.51	0.575	0.71
L1	0.125	REF	
M	3.00	3.40	3.80
θ	0 °	---	12 °

RECOMMENDED  
SOLDERING FOOTPRINT\*

DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)