Part Number : 1600130623
Product Description : stAK50h 2 Bay Infotainment Hybrid Header, 56 Circuits, Bay A: 28 Circuit/Key 2; Bay B: 28 Circuit/Key 3; 2.10mm PC Tail Length, UL 94 HB, Gray, Tube
Series Number : 160013
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

1600130623_sd.pdf

PK-31302-235-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

AS-160013-001-001.pdf

PS-160013-001-001.pdf

TS-160013-2291-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	160013
Description	stAK50h 2 Bay Infotainment Hybrid Header, 56 Circuits, Bay A: 28 Circuit/Key 2; Bay B: 28 Circuit/ Key 3; 2.10mm PC Tail Length, UL 94 HB, Gray, Tube
Application	Automotive, Wire-to-Board
Component Type	PCB Header
Product Name	stAK50h
UPC	191130043323

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Breakaway	No
Circuits (Loaded)	56
Circuits (maximum)	56
Color - Resin	Gray

Downloaded from Arrow.com.

Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	12.846/g
Number of Rows	5
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	Yes
PC Tail Length	2.10mm
Pitch - Mating Interface	2.00mm, 4.00mm
Pitch - Termination Interface	2.00mm, 4.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Sealed	Unsealed
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole
Terminal Size	0.5, 1.2

Mates With / Use With

Mates with Part(s)

Description	Part Number
stAK50h Hybrid Receptacle, 28 Circuits, Key 2, Light Green, Bag	1600140012
stAK50h Hybrid Receptacle, 28	1600140013

Downloaded from Arrow.com.

Circuits, Key 3, Light Gray, Bag	

This document was generated on Oct 07, 2026

Downloaded from Arrow.com.