



**Part Number :** [39000210](#)

**Product Description :** Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 28-22 AWG, Bag

**Series Number :** 5556

**Status :** Active

**Product Category :** Crimp Terminals

**Engineering Part Number :** 5556-S2PL

**Packaging Alternative :** [39000209](#) (Reel)



---

## Documents and Resources

### Drawings

[039000210\\_sd.pdf](#)

[PK-5556-003-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[55560001-AS-000.pdf](#)

[55560002-AS-000.pdf](#)

[55560002-PS-CH-000.pdf](#)

[55560002-PS-ES-000.pdf](#)

[55560002-PS-SK-000.pdf](#)

[PS-5556-001-001.pdf](#)

[PS-5556-002-001.pdf](#)

[55560001-TS-000.pdf](#)

[55560010-TS-000.pdf](#)

[TS-5556-002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	5556
Description	Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 28-22 AWG, Bag
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Mini-Fit
UPC	800754396059

### Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

## Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.140/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm <sup>2</sup>	N/A

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Mini-Fit Jr. Receptacle Housings	<u>5557</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>44516</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>42474</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>43760</u>
Mini-Fit Jr. Dual Row Receptacle Housings	<u>46992</u>

---

## Application Tooling

## Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 28-22 AWG	<u>638191000</u>

---

This document was generated on May 27, 2026