

Product Status	Production
Applications	Automotive Grade
	AEC-Q200
Feature	Multilayer
	Non-Mag Core
	Non-Magnetic Core (Dielectric Ceramic)
	High Q
Series   Type	MLG-P
Brand	TDK
Environmental Compliance	 RoHS  REACH  Halogen Free  Lead Free



Size	
Length(L)	0.60mm $\pm 0.03$ mm
Width(W)	0.30mm $\pm 0.03$ mm
Thickness   Height	0.30mm $\pm 0.03$ mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics	
Inductance	33nH $\pm 5\%$ at 300MHz
Rated Current	130mA
DC Resistance [Typ.]	1.55Ω
DC Resistance [Max.]	2.2Ω
Self Resonant Frequency [Min.]	1.8GHz
Self Resonant Frequency [Typ.]	2.4GHz
Q [Min.]	10 at 300MHz
Q [Typ.]	13 at 300MHz

Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow
AEC-Q200	YES
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g





! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG0603P33NJT25

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.