



JMSCD-12XMS Product Details



Share



Print



Email



 Active

 View 3D PDF

Military/Aerospace High Performance Relays

JMSCD-12XMS = M39016/16-043M

JMSCD-12XMS (1617128-3)

TE Internal Number: 1617128-3

Product Highlights [View All](#)

- MSD TO-5 Relay Series
- Input Voltage = 12 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 1 A
- Non Polarized, Monostable Coil - Magnetic System

Pricing & Availability



Request Sample



Add to My Part List



Buy Product through
Distributor



Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

MOSFET DriverWithout

Mechanical Attachment

Mounting OptionsPC Board

Electrical Characteristics

Input Voltage (VDC)12

Contact - Rated Current (A)1

Coil Suppression DiodeWith

Coil Polarity Protection DiodeWithout

Coil - Resistance (Ω)850

Coil Power MeasurementMilliwatts

Coil - Rated Power, DC (mW)169

Actuating SystemDC

Shock75 G's, 6ms

Vibration30G's, 10 to 3000Hz

Termination Features

Termination TypeLong Leads

Body Features

Enclosure TypeHermetically Sealed

Contact Features

Pin Configuration.200" x .300" Spreader Pad

Configuration Features

Contact - Arrangement2 Form C, DPDT, 2 C/O

Coil - Magnetic SystemNon Polarized, Monostable

Transistor DriverWithout

Industry Standards

Government/Industry QualificationYes

Government/Industry Part NumberM39016/16-043M

RoHS/ELV ComplianceNot ELV/RoHS compliant

Lead Free Solder ProcessesNot suitable for lead free processing

Approved StandardsM39016 Qualified, M Level

Conditions for Usage

Temperature Range (°C)-65 - +125

Other

SeriesMSD TO-5 Relay

BrandCOMACC

Related Products

Not quite the product
you're looking for?

[Find Similar Products](#)

[View Part in Product
Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

