

CK1,6-ED-2,50BU AG - Crimp contact

1663446

<https://www.phoenixcontact.com/us/products/1663446>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14

Commercial data

Item number	1663446
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AIA
Catalog page	Page 507 (C-2-2019)
GTIN	4017918123253
Weight per piece (including packing)	0.74 g
Weight per piece (excluding packing)	0.677 g
Customs tariff number	85366990
Country of origin	DE

CK1,6-ED-2,50BU AG - Crimp contact

1663446

<https://www.phoenixcontact.com/us/products/1663446>



Technical data

Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
---------	--

Mounting

Assembly note	At voltages of < 5 V and currents < 5 mA, gold-plated contacts are recommended.
	The quality of a crimp connection is determined by DIN EN 60352-2.

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	2.5 mm ² ... 2.5 mm ²
Connection cross section AWG	14
Stripping length of the individual wire	6 mm
Conductor cross section flexible	2.5 mm ² ... 2.5 mm ²

Material specifications

Contact material	Copper alloy
Contact surface material	silver-plated

Dimensions

Mechanical characteristics	
Contact diameter	1.6 mm

CK1,6-ED-2,50BU AG - Crimp contact

1663446

<https://www.phoenixcontact.com/us/products/1663446>



Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ED-2,50BU AG - Crimp contact




1663446

<https://www.phoenixcontact.com/us/products/1663446>

Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-2,50BU AG - Crimp contact

1663446

<https://www.phoenixcontact.com/us/products/1663446>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1663446>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: EAC-Zulassung

CK1,6-ED-2,50BU AG - Crimp contact

1663446

<https://www.phoenixcontact.com/us/products/1663446>



Classifications

ECLASS

ECCLASS-13.0	27440204
--------------	----------

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-2,50BU AG - Crimp contact

1663446

<https://www.phoenixcontact.com/us/products/1663446>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com