



**Part Number :** [1300080316](#)

**Product Description :** Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 22-18 AWG, Black PUR Cable, 10.0m (32.81') Length

**Series Number :** 130008

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 303001P80M100



---

## Documents and Resources

### Drawings

[1300080316 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 22-18 AWG, Black PUR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Single Ended
UPC	78678853541

#### Electrical

Current - Maximum per Contact	2.0A, 3.0A
Voltage - Maximum	300V AC/DC

#### Physical

Cable Diameter	11.43mm (.450")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	TPE

Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1909.622/g
Orientation	90° to Pigtail
Poles	19
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	18, 22

---

This document was generated on May 27, 2026