Part Number : 2270060003
Product Description : Sentrality 3.40mm Press-Fit Pin, 26.00mm Length, Bag
Series Number : 227006
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2270060003_sd.pdf

2032630006-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2043130018-AS-000.pdf

2043130018-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	227006
Description	Sentrality 3.40mm Press-Fit Pin, 26.00mm Length, Bag
Application	Board-to-Board
Component Type	PCB Header
Product Name	Sentrality
UPC	198282540496

Electrical

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	No

Downloaded from Arrow.com.

Height Above Board	26.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	5.601/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Top-entry Knurled Press-Fit Socket Assemblies with Self-alignment Capability	204313
Sentrality Top-entry Knurled Press-Fit Socket Assemblies	204316
Sentrality Top-entry Surface Mount Socket Assemblies	204318
Sentrality Top-entry Surface Mount Socket Assemblies with Self-alignment Capability	204365
Sentrality Top-entry Surface Mount Socket Assemblies	212194
Sentrality Surface Mount Socket Assemblies	212195
Sentrality 3.40mm Right-Angle Socket Assemblies	205000

Downloaded from Arrow.com.