


PRODUCT NUMBER	PITCH
HWxx50x200J0G	5.08 mm






N=Number of Poles
 Dim P=(N-1)×5.08
 Dim L=N×5.08
 Dim A=N×5.08+0.5
 Dim B=(N-1)×5.08+10.16
 Dim C=(N-1)×5.08+15.24

Poles	Dim L	Dim P	Dim A	Dim B	Dim C
2P-6P	±0.15	±0.10	±0.15	±0.10	±0.15
7P-12P	±0.20	±0.15	±0.20	±0.15	±0.20
13P-18P	±0.25	±0.20	±0.25	±0.20	±0.25
19P-24P	±0.30	±0.25	±0.30	±0.25	±0.30

PART NO.: HW xx 50 x 2 00J0 G

Solid block	0	Black (RAL9005)	RoHS compliant
No. of poles	2	Red (RAL3001/D)	(lead<4%)
02 2 poles	3	Orange(RAL2011/P)	In copper Alloy
03 3 poles	4	Yellow(RAL1018/A)	
... ..	5	Green(RAL6018/T)	
24 24 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	




Material:

- Item①Top body:Thermoplastic (UL94V-0)
- Item②Bottom body:Thermoplastic (UL94V-0)
- Item③Terminal lever:Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item④Spring clamp:Stainless Steel
- Item⑤Female contact:PhBz (CuSn) Tin plated
- Item⑥Flange screw:Steel M2.5 plated zinc

Electrical cULus

- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:8-9mm
- Withstanding Voltage:1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 



mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK													
ltr ecn no dr date				tolerances unless otherwise specified								title											
				angles lineal		X.±0.5						TERMINAL BLOCK											
						X.X±0.3						SPRING CLAMP, PLUGGABLE PLUG, WITH FLANGE											
						X°.±1°						CONTACT ON DOWN SIDE											
				dr		EVIN ZHONG		051514				dwg no				sheet 1 of 1				size			
				engr		EVIN ZHONG		051514				HWxx50x200J0G								A4			
				chr		HANKE FENG		051514															
				appd		SHI JUN		051514															
sheet index		revision		A																			
sheet		sheet		1																			