

Data Sheet | Item Number: 224-114

2-conductor lighting connector; push-button on lighting side; Lighting side: for all conductor types; Inst. side: for solid conductors; 224 Series; max. 2.5 mm²; Surrounding air temperature: max 75°C; 2,50 mm²; black

<https://www.wago.com/224-114>



Color: ■ black

Lighting connector, 224 Series, Push-in

Quick and easy connections are guaranteed with this lighting connector (item number 224-114). WAGO's 224 Series lighting connectors make connecting lights a breeze—and completely safe. Light up any space quickly and reliably. If you need to connect a fine-stranded conductor with a solid conductor, choose the 224 Series for performance you can trust. Strip lengths must be between 9 and 11 mm when connecting conductors to this lighting connector. Our splicing connector is rated for 400 V and is designed for use with a rated current of up to 24 A. It is therefore suitable for high-load applications. Featuring conductor terminals along with PUSH WIRE® as well as CAGE CLAMP®, this connector outperforms the competition. Our trusted PUSH WIRE® connection offers the fastest method for clamping conductors. It utilizes the conductor's stiffness to overcome the clamping spring's contact force. Our reliable and maintenance-free CAGE CLAMP® connection makes it easy to connect all types of conductors without having to prepare the conductor. For example, you don't need to crimp ferrules. The item's dimensions are (9.5 x 15.5 x 20.5) mm (width x height x depth). Depending on the type of conductor, this lighting connector is suitable for conductor cross sections ranging from 1 mm² to 2.5 mm² on one side and for conductor cross sections from 0.5 mm² to 2.5 mm² on the other side.

Notes	
Safety Information	in grounded power lines

Electrical data				
Ratings per		EN 60664		
Overvoltage category	III	III	II	
Pollution degree	3	2	2	
Nominal voltage	-	-	400 V	
Rated impulse withstand voltage	-	-	4 kV	
Rated current	-	-	24 A	

General information	
Wiring direction	Side-entry wiring



Connection Data

Clamping units	3
Total number of potentials	1

Connection 1

Connection type	Installation side
Connection technology	PUSH WIRE®
Number of connection points	2
Actuation type	Push-in
Connectable conductor materials	Copper Aluminum

Connectable conductor materials (note)	Terminating Aluminum Conductors (not for use in North America) WAGO Spring-Clamp Terminal Blocks are also suitable for solid aluminum conductors up to 4 mm²/12 AWG if WAGO Aluminum Contact Paste 249-130 is used for termination. Aluminum Contact Paste Advantages: ▪ Automatically destroys the oxide film during clamping. ▪ Prevents fresh oxidation at the clamping point. ▪ Prevents electrolytic corrosion between aluminum and copper conductors (in the same terminal block). ▪ Provides long-term protection against corrosion. Using terminal blocks with CAGE CLAMP® Spring Pressure Connection Technology, aluminum conductors must first be cleaned with a blade and then immediately inserted into the clamping units filled with aluminum contact paste. For spring clamp connections with PUSH WIRE® connection technology, WAGO recommends that the aluminum conductor first be cleaned and then immediately inserted into the clamping unit filled with aluminum contact paste. It is also possible to apply WAGO Aluminum Contact Paste additionally on the whole surface of the aluminum conductor before termination. Please note that the nominal currents must be adapted to the reduced conductivity of the aluminum conductors:: 2.5 mm² = 16 A 4 mm² = 22 A
Solid conductor	1 ... 2.5 mm² / 16 ... 14 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 inches
Wiring direction	Side-entry wiring

Connection 2

Connection type	Lighting side
Connection technology	CAGE CLAMP®
Number of connection points	1
Solid conductor	0.5 ... 2.5 mm² / 20 ... 14 AWG
Fine-stranded conductor	0.5 ... 2.5 mm² / 20 ... 16 AWG



Physical data	
Width	9.5 mm / 0.374 inches
Height	15.5 mm / 0.61 inches
Depth	20.5 mm / 0.807 inches

Material data	
Note (material data)	Information on material specifications can be found here
Color	black
Fire load	0.045 MJ
Weight	2.5 g

Environmental requirements	
Ambient temperature (operation)	+75 °C
Continuous operating temperature	120 °C

Commercial data	
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	CH
GTIN	4044918583787
Customs tariff number	85369010000

Product Classification	
UNSPSC	39121409
eCl@ss 10.0	27-14-11-03
eCl@ss 9.0	27-14-11-03
ETIM 9.0	EC000446
ETIM 10.0	EC000446
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
  					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2	154112	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UL UL International Germany GmbH	EN 60998	CCA-2617-A1	UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UL UL International Germany GmbH	EN 60998	D-05895-A1 (EN60998-1 EN60998-2-2)			
VDE VDE Prüf- und Zertifizierungsinstitut	EN 60998	40022792			



Approvals for marine applications



Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	-	23-2417173-PDA
LR Lloyds Register	EN 60998	LR22207029TA
PRS Polski Rejestr Statków	EN 60998	TE/1093/880590/23

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 224-114



Documentation

Bid Text			
224-114	19.02.2019	xml 3.51 KB	
224-114	21.02.2019	docx 15.71 KB	

CAD/CAE-Data

CAD data
2D/3D Models 224-114



CAE data
EPLAN Data Portal 224-114
WSCAD Universe 224-114
ZUKEN Portal 224-114




1 Compatible Products
1.1 Optional Accessories
1.1.1 Tool
1.1.1.1 Aluminum contact paste



Item No.: 249-130
Syringe; Contents: Aluminum Contact Paste,
20 ml

Installation Notes


Conductor termination



Lighting Connectors (2.5 mm²), 224 Series

Strip conductor to 9 ... 11 mm (0.35 ... 0.43 inch).



Conductor termination



To connect: Press button fully, insert stripped conductor into square entry and release.

To remove: Press button and withdraw conductor.


Conductor termination



To connect: Insert stripped solid conductor into circular entry and push until it hits the backstop.

To remove: Hold conductor to be removed and twist alternately left and right while slightly pulling the connector.

Testing



Testing via separate test ports.

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com