





Color: ■ yellow

Luminaire disconnect connector, 873 Series, Push-in

This luminaire disconnect connector (item number 873-902) is designed for seamless electrical installations. Conductors should only be connected to this luminaire disconnect connector if their strip length is between 11 and 13 mm . This product features conductor terminals and utilizes PUSH WIRE® as well as PUSH WIRE®. Our PUSH WIRE® connection offers a quick and simple method for connecting solid conductors. Dimensions: (13 x 13.2 x 42) mm (width x height x depth). Depending on the type of conductor, this luminaire disconnect connector is suitable for conductor cross sections ranging from 0.75 mm² to 4 mm².

Notes	
Note	Touch-proof connectors are required for the ballast supply cables in fluorescent lighting fixtures in the USA and Canada. When replacing the ballast, the touch-proof connector is disconnected, the ballast is replaced, and the connection to the power supply is restored by re-connecting the connector. Reconnection streamlines ballast replacement while enhancing safety by safeguarding the installer from electric shock. The 873 Series Luminaire Disconnect Connectors are approved according to UL 2459 and CSA 22.2 for this type of application.

Electrical data			
Ratings per		EN 60998	
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	-	400 V
Rated impulse withstand voltage	-	-	4 kV
Rated current	-	-	6 A

Ratings per		EN 61984	
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	-	-
Rated impulse withstand voltage	-	-	-
Rated current	-	-	-

Connection Data	
Clamping units	6
Total number of potentials	2

Connection 1	
Connection type	Plug
Connection technology	PUSH WIRE®
Actuation type	Push-in
Connectable conductor materials	Copper
Solid conductor	0.75 ... 4 mm ² / 18 ... 12 AWG
Stranded conductor	16 ... 12 AWG
Strip length	11 ... 13 mm / 0.43 ... 0.51 inches
Pole number	2



Connection 2	
Connection type	Socket
Connection technology	PUSH WIRE®
Actuation type	Push-in
Solid conductor	18 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 inches

Physical data	
Width	13 mm / 0.512 inches
Height	13.2 mm / 0.52 inches
Depth	42 mm / 1.654 inches

Mechanical data	
Marking	1 2

Material data	
Note (material data)	Information on material specifications can be found here
Color	yellow
Fire load	0.093 MJ
Weight	4.8 g

Commercial data	
Product Group	8 (Misc. Chassis Mount Blocks)
PU (SPU)	400 (40) pcs
Packaging type	Box
Country of origin	CN
GTIN	4045454548421
Customs tariff number	85366990990

Product Classification	
UNSPSC	39121421
eCl@ss 10.0	27-44-03-14
eCl@ss 9.0	27-44-03-14
ETIM 9.0	EC002560
ETIM 10.0	EC002560
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption



Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
CCA KEMA KEUR CCA SP KEMA KEUR UL LISTED SEPARABLE DISCONNECT 2017					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 61984	NTR NL-7390	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
CCA DEKRA Certification B.V.	EN 60998	71-114174	UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-
CCA DEKRA Certification B.V.	EN 60998	NTR NL-8088			
CSA DEKRA Certification B.V.	C22.2 No. 182.3	1961671			
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71-156292 REV.1			
UL Underwriters Laboratories Inc.	UL 2459	E313353			

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 873-902	↓

Documentation

Bid Text			
873-902	19.02.2019	xml 3.11 KB	↓
873-902	21.02.2019	docx 14.78 KB	↓

CAD/CAE-Data

CAD data		CAE data	
2D/3D Models 873-902	↓	ZUKEN Portal 873-902	↓

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com