






Register to Get  Shipping Coupon

 0

 LOGIN/SIGN UP

HOMECOMMUNITY **NEW**FORUMWIKIBLOGPRODUCT LINES EDUCATION\$USDWISH LIST

[Sensors](#) / [Flex Sensors](#) / [RP-C18.3-ST Thin Film Pressure Sensor](#)


RP-C18.3-ST Thin Film Pressure Sensor

SKU:SEN0294 Brand:Other Reward Points: 50


* Model:

Quantity: **ADD TO CART**


Frequently Bought Together




+



+



+




RP-C18.3-ST Thin Film Pressure Sensor

For... Resistor - Small

Flex... Sensor - 100lbs

RP-C18.3-ST Thin



You have chosen:0
Total amount:

BUY IT NOW

INTRODUCTION

This is a circular flexible thin film pressure sensor of short legs with a diameter of 18.3mm, which can be used to realize highly sensitive detection of pressure. The sensor is durable and designed to sense static and dynamic pressure in a high respond speed. Its advantages of recording the intensity and frequency of force make it widely used in all kinds of applications, such as, pressure switch, bed monitoring system, intelligent sneaker and medical device system. These sensors are also very easy to use.

RP-C flexible pressure sensor is made of ultra-thin film of excellent mechanical property, excellent conductive materials and nanometre pressure sensitive layers. There are thin film and pressure sensitive layer on the upper layer of the sensor, and thin film and conductive circuit on the lower layer. These two layers are glued together by double sided tape. When outside pressure applies to the active area, the disconnected circuit of the lower layer will be connected through the pressure sensitive layer of the upper layer, by which to convert pressure into resistance. The output resistance decreases as pressure increases.

RP-C18.3-LT Dimension Diagram

Force vs Resistance

SPECIFICATION

Downloaded from [Arrow.com](#)

- Thickness: 0.4mm
- Trigger Force: 20g, triggered (default resistance<200kΩ)
- Pressure Measuring Range: 20g~6kg
- Static Pressure & Dynamic Pressure Measurement (within the frequency of 10Hz)
- Initial Resistance: >10MΩ
- Activation Time: <0.01S
- Operating Temperature: -40°C~+85°C
- Lifespan: >1million times
- Hysteresis: +10%, (RF+ -RF-)/FR+, 1000g Force
- Response Time: <10ms
- EMI: Not generate
- EDS: Not generate
- Drift: <5%, 2.5Kg Force, Static load 24H

DOCUMENTS

- [Wiki](#)

SHIPPING LIST

- RP-C18.3-ST Thin Film Pressure Sensor x1

REVIEW

FAQ

0 Comments

DFRobot

Disqus' Privacy Policy

Login

Recommend

Tweet

Share

Sort by Best

 Start the discussion...

Be the first to comment.

Subscribe

Add Disqus to your site

Do Not Sell My Data

DISQUS

Sign up for exclusive offers!

Your email address

→

Like us on

f

🐦

G+

YouTube

in



INFORMATION	CUSTOMER SERVICE	MY ACCOUNT
About Us	DFRobot Distributors	Affiliates
Warranty	Contact us	Specials
Privacy Policy	Site Map	Coupon
Shipping		
Payment		
FAQ		